

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P366152

Luminaire Tested: **FLD6BX30D010-FEU6B35-8027-F6LBXVM1-WMH-BL87**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P366152
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-47)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX30D010-FEU6B35-8027-F6LBXVM1-WMH-BL87
Description: VANDAL RESISTANT ENCLOSED BOTTOM LENS, WARM HAZE REFLECTOR, BOTTOM LENS POLYCARBONATE, CLEAR 0.375", 3000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2320.0 lumens
Efficiency: N/A
Efficacy: 85.9 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.85
Luminous Opening: Circular (Dia: 0.71' x H: 0')
CIE Type: Direct


Input Watts (W): 27
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P366152

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8027-F6LBXVM1-WMH-BL87

Luminous Intensity Polar Plot





TEST NUMBER: P366152

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8027-F6LBXVM1-WMH-BL87

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	108	104	100	97	106	102	98	95	99	96	93		96	93	91		93	91	89	88
3	103	97	92	88	101	96	91	88	93	89	86		91	88	85		88	86	84	82
4	98	91	86	82	96	90	85	81	88	83	80		86	82	79		84	81	78	77
5	93	85	80	76	92	85	79	75	83	78	75		81	77	74		80	76	73	72
6	89	80	75	71	88	80	74	70	78	73	70		77	73	69		76	72	69	68
7	85	76	70	66	83	75	70	66	74	69	65		73	68	65		72	68	65	63
8	81	72	66	62	80	71	66	62	70	65	62		69	65	61		68	64	61	60
9	77	68	62	58	76	67	62	58	66	62	58		66	61	58		65	61	58	56
10	74	64	59	55	73	64	59	55	63	58	55		62	58	55		62	58	55	53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	81615
5°	81272
10°	77205
15°	70129
20°	61023
25°	51881
30°	40811
35°	23285
40°	10476
45°	4412
50°	1390
55°	424
60°	290
65°	226
70°	216
75°	285
80°	142
85°	282



TEST NUMBER: P366152

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8027-F6LBXVM1-WMH-BL87

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	277.2	12.0
10°-20°	689.8	29.7
20°-30°	781.7	33.7
30°-40°	453.2	19.5
40°-50°	100.5	4.3
50°-60°	11.0	0.5
60°-70°	3.6	0.2
70°-80°	2.4	0.1
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1748.8	75.4
0°-40°	2201.9	94.9
0°-60°	2313.4	99.7
0°-90°	2320.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2320.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2988	
5°	2964	277
15°	2480	690
25°	1721	782
35°	698	453
45°	114	100
55°	9	11
65°	4	4
75°	3	2
85°	1	1
90°	0	



TEST NUMBER: P366152

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8027-F6LBXVM1-WMH-BL87

CANDELA DISTRIBUTION (FULL):

	0°
0°	2987.9
2.5°	2990.6
5°	2964.0
7.5°	2899.4
10°	2783.5
12.5°	2642.8
15°	2479.9
17.5°	2308.2
20°	2099.3
22.5°	1910.8
25°	1721.4
27.5°	1519.6
30°	1293.9
32.5°	1027.5
35°	698.3
37.5°	448.7
40°	293.8
42.5°	192.1
45°	114.2
47.5°	63.7
50°	32.7
52.5°	15.0
55°	8.9
57.5°	7.1
60°	5.3
62.5°	4.4
65°	3.5
67.5°	2.7
70°	2.7
72.5°	2.7
75°	2.7
77.5°	1.8
80°	0.9
82.5°	0.9
85°	0.9
87.5°	0.0
90°	0.0

(END OF REPORT)