

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P366102

Luminaire Tested: **FLD6BX20D010-FEU6B12-8035-F6LBXVM1-WMH-BTR80**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P366102
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-29)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX20D010-FEU6B12-8035-F6LBXVM1-WMH-BTR80
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, WARM HAZE REFLECTOR,
BOTTOM TRIM ACRYLIC, PATTERN 12 0.125", 2000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1554.9 lumens
Efficiency: N/A
Efficacy: 76.6 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.88
Luminous Opening: Circular (Dia: 0.44' x H: 0')
CIE Type: Direct


Input Watts (W): 20.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P366102

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8035-F6LBXVM1-WMH-BTR80

Luminous Intensity Polar Plot





TEST NUMBER: P366102

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8035-F6LBXVM1-WMH-BTR80

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	109	106	104	110	107	105	102	103	101	99		99	98	96		96	95	93	91
2	106	100	96	92	104	98	94	91	95	92	89		92	89	87		89	87	85	83
3	100	92	86	82	97	91	85	81	88	84	80		85	82	79		83	80	77	76
4	94	85	79	74	92	84	78	73	82	77	72		79	75	72		78	74	71	69
5	88	79	72	67	86	78	71	67	76	70	66		74	69	66		72	68	65	63
6	83	73	66	62	82	72	66	61	71	65	61		69	64	60		68	63	60	58
7	79	68	61	57	77	67	61	57	66	60	56		65	60	56		64	59	56	54
8	74	64	57	52	73	63	57	52	62	56	52		61	56	52		60	55	52	50
9	70	60	53	49	69	59	53	49	58	53	49		57	52	48		56	52	48	47
10	67	56	50	46	66	56	50	46	55	49	45		54	49	45		53	49	45	44

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	110825
5°	108539
10°	102611
15°	93779
20°	82392
25°	70029
30°	57288
35°	45095
40°	33602
45°	23827
50°	16809
55°	12071
60°	8650
65°	6269
70°	4878
75°	3984
80°	3381
85°	3368



TEST NUMBER: P366102

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8035-F6LBXVM1-WMH-BTR80

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	141.0	9.1
10°-20°	352.0	22.6
20°-30°	404.9	26.0
30°-40°	323.1	20.8
40°-50°	186.3	12.0
50°-60°	88.8	5.7
60°-70°	38.4	2.5
70°-80°	15.7	1.0
80°-90°	4.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	898.0	57.8
0°-40°	1221.1	78.5
0°-60°	1496.2	96.2
0°-90°	1554.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1554.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1548	
5°	1510	141
15°	1265	352
25°	886	405
35°	516	323
45°	235	186
55°	97	89
65°	37	38
75°	14	16
85°	4	5
90°	0	



TEST NUMBER: P366102

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8035-F6LBXVM1-WMH-BTR80

CANDELA DISTRIBUTION (FULL):

	0°
0°	1547.8
2.5°	1538.2
5°	1510.1
7.5°	1468.2
10°	1411.3
12.5°	1344.7
15°	1265.1
17.5°	1178.7
20°	1081.3
22.5°	983.2
25°	886.4
27.5°	788.3
30°	692.9
32.5°	605.8
35°	515.9
37.5°	435.7
40°	359.5
42.5°	294.3
45°	235.3
47.5°	188.7
50°	150.9
52.5°	120.8
55°	96.7
57.5°	76.2
60°	60.4
62.5°	47.3
65°	37.0
67.5°	29.5
70°	23.3
72.5°	18.5
75°	14.4
77.5°	11.0
80°	8.2
82.5°	6.2
85°	4.1
87.5°	2.7
90°	0.0

(END OF REPORT)