

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P364727

Luminaire Tested: **FLD6BX30D010-FEU6B35-8030-F6LBXVM1-LI-BL84**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P364727
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-43)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX30D010-FEU6B35-8030-F6LBXVM1-LI-BL84
Description: VANDAL RESISTANT ENCLOSED BOTTOM LENS, SPECULAR CLEAR REFLECTOR,
BOTTOM LENS POLYCARBONATE, CLEAR 0.125", 3000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2601.0 lumens
Efficiency: N/A
Efficacy: 96.3 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.82
Luminous Opening: Circular (Dia: 0.71' x H: 0')
CIE Type: Direct


Input Watts (W): 27
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P364727

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8030-F6LBXVM1-LI-BL84

Luminous Intensity Polar Plot





TEST NUMBER: P364727

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8030-F6LBXVM1-LI-BL84

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94
2	109	104	100	97	106	102	99	96	99	96	94	96	94	92	93	91	90	88
3	103	97	93	89	101	96	92	88	93	90	87	91	88	85	89	86	84	83
4	99	91	86	82	97	90	85	82	88	84	81	86	83	80	84	81	79	77
5	94	86	80	76	92	85	80	76	83	79	75	82	78	75	80	77	74	73
6	90	81	75	71	88	80	75	71	79	74	71	77	73	70	76	73	70	68
7	85	77	71	67	84	76	71	67	75	70	66	74	69	66	72	69	66	64
8	82	72	67	63	80	72	67	63	71	66	63	70	65	62	69	65	62	61
9	78	69	63	59	77	68	63	59	67	62	59	66	62	59	66	62	59	57
10	74	65	60	56	74	65	60	56	64	59	56	63	59	56	63	58	56	54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	100072
5°	98168
10°	90657
15°	80784
20°	68991
25°	57942
30°	45485
35°	23569
40°	11257
45°	4431
50°	1164
55°	329
60°	213
65°	187
70°	160
75°	211
80°	157
85°	313



TEST NUMBER: P364727

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8030-F6LBXVM1-LI-BL84

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	332.0	12.8
10°-20°	794.0	30.5
20°-30°	876.6	33.7
30°-40°	482.3	18.5
40°-50°	101.9	3.9
50°-60°	8.6	0.3
60°-70°	2.7	0.1
70°-80°	1.9	0.1
80°-90°	1.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2002.5	77.0
0°-40°	2484.9	95.5
0°-60°	2595.4	99.8
0°-90°	2601.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2601.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3664	
5°	3580	332
15°	2857	794
25°	1922	877
35°	707	482
45°	115	102
55°	7	9
65°	3	3
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P364727

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8030-F6LBXVM1-LI-BL84

CANDELA DISTRIBUTION (FULL):

0°	
0°	3663.6
2.5°	3661.6
5°	3580.2
7.5°	3454.7
10°	3268.5
12.5°	3083.2
15°	2856.7
17.5°	2626.4
20°	2373.4
22.5°	2151.9
25°	1922.5
27.5°	1700.9
30°	1442.1
32.5°	1100.9
35°	706.8
37.5°	476.4
40°	315.7
42.5°	197.0
45°	114.7
47.5°	58.8
50°	27.4
52.5°	11.8
55°	6.9
57.5°	4.9
60°	3.9
62.5°	2.9
65°	2.9
67.5°	2.0
70°	2.0
72.5°	2.9
75°	2.0
77.5°	1.0
80°	1.0
82.5°	1.0
85°	1.0
87.5°	1.0
90°	0.0

(END OF REPORT)