

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P364738

Luminaire Tested: **FLD6BX30D010-FEU6B35-8030-F6LBXVM1-LI-BTR85**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P364738
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-24)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX30D010-FEU6B35-8030-F6LBXVM1-LI-BTR85
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, SPECULAR CLEAR REFLECTOR, BOTTOM TRIM POLYCARBONATE, CLEAR 0.187", 3000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2201.0 lumens
Efficiency: N/A
Efficacy: 81.5 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.77
Luminous Opening: Circular (Dia: 0.44' x H: 0')
CIE Type: Direct


Input Watts (W): 27
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P364738

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8030-F6LBXVM1-LI-BTR85

Luminous Intensity Polar Plot





TEST NUMBER: P364738

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8030-F6LBXVM1-LI-BTR85

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	109	104	100	97	107	102	99	96	99	96	94		96	94	92		94	92	90	89
3	104	98	93	90	102	97	92	89	94	90	87		92	89	86		89	87	85	83
4	99	92	87	83	97	91	86	83	89	85	82		87	84	81		85	82	80	78
5	95	87	82	78	93	86	81	77	84	80	77		83	79	76		81	78	75	74
6	91	82	77	73	89	82	76	73	80	76	72		79	75	72		78	74	71	70
7	87	78	73	69	85	77	72	69	76	72	68		75	71	68		74	70	68	66
8	83	74	69	65	82	74	68	65	73	68	65		72	67	64		71	67	64	63
9	79	71	65	62	78	70	65	61	69	65	61		68	64	61		68	64	61	60
10	76	67	62	58	75	67	62	58	66	61	58		65	61	58		65	61	58	57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	247034
5°	241408
10°	222547
15°	197113
20°	166879
25°	132213
30°	92914
35°	38696
40°	13282
45°	3544
50°	1949
55°	1823
60°	1675
65°	1643
70°	1633
75°	1881
80°	2392
85°	4026



TEST NUMBER: P364738

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8030-F6LBXVM1-LI-BTR85

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	311.2	14.1
10°-20°	737.7	33.5
20°-30°	757.3	34.4
30°-40°	320.7	14.6
40°-50°	39.4	1.8
50°-60°	13.1	0.6
60°-70°	9.6	0.4
70°-80°	7.5	0.3
80°-90°	4.5	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1806.2	82.1
0°-40°	2126.9	96.6
0°-60°	2179.4	99.0
0°-90°	2201.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2201.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3450	
5°	3359	311
15°	2659	738
25°	1674	757
35°	443	321
45°	35	39
55°	15	13
65°	10	10
75°	7	7
85°	5	4
90°	0	



TEST NUMBER: P364738

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8030-F6LBXVM1-LI-BTR85

CANDELA DISTRIBUTION (FULL):

0°	
0°	3450.1
2.5°	3427.7
5°	3358.7
7.5°	3240.0
10°	3060.9
12.5°	2870.2
15°	2659.1
17.5°	2432.4
20°	2190.1
22.5°	1932.3
25°	1673.5
27.5°	1405.9
30°	1123.8
32.5°	792.0
35°	442.7
37.5°	253.9
40°	142.1
42.5°	74.9
45°	35.0
47.5°	20.4
50°	17.5
52.5°	15.6
55°	14.6
57.5°	13.6
60°	11.7
62.5°	10.7
65°	9.7
67.5°	8.8
70°	7.8
72.5°	7.8
75°	6.8
77.5°	6.8
80°	5.8
82.5°	5.8
85°	4.9
87.5°	2.9
90°	0.0

(END OF REPORT)