

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P364675

Luminaire Tested: **FLD6BX20D010-FEU6B12-8040-F6LBXVM1-LI-BL86**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P364675
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-43)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX20D010-FEU6B12-8040-F6LBXVM1-LI-BL86
Description: VANDAL RESISTANT ENCLOSED BOTTOM LENS, SPECULAR CLEAR REFLECTOR,
BOTTOM LENS POLYCARBONATE, CLEAR 0.250", 2000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1810.0 lumens
Efficiency: N/A
Efficacy: 89.2 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.82
Luminous Opening: Circular (Dia: 0.71' x H: 0')
CIE Type: Direct


Input Watts (W): 20.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P364675

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8040-F6LBXVM1-LI-BL86

Luminous Intensity Polar Plot





TEST NUMBER: P364675

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8040-F6LBXVM1-LI-BL86

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	109	104	100	97	106	102	99	96	99	96	94		96	94	92		93	91	90	88
3	103	97	93	89	101	96	92	88	93	90	87		91	88	85		89	86	84	83
4	99	91	86	82	97	90	85	82	88	84	81		86	83	80		84	81	79	77
5	94	86	80	76	92	85	80	76	83	79	75		82	78	75		80	77	74	73
6	90	81	75	71	88	80	75	71	79	74	71		77	73	70		76	73	70	68
7	85	77	71	67	84	76	71	67	75	70	66		74	69	66		72	69	66	64
8	82	72	67	63	80	72	67	63	71	66	63		70	65	62		69	65	62	61
9	78	69	63	59	77	68	63	59	67	62	59		66	62	59		66	62	59	57
10	74	65	60	56	74	65	60	56	64	59	56		63	59	56		63	58	56	54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	69638
5°	68313
10°	63087
15°	56218
20°	48009
25°	40320
30°	31651
35°	16403
40°	7834
45°	3083
50°	812
55°	229
60°	148
65°	129
70°	112
75°	148
80°	110
85°	219



TEST NUMBER: P364675

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8040-F6LBXVM1-LI-BL86

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	231.0	12.8
10°-20°	552.5	30.5
20°-30°	610.0	33.7
30°-40°	335.7	18.5
40°-50°	70.9	3.9
50°-60°	6.0	0.3
60°-70°	1.8	0.1
70°-80°	1.4	0.1
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1393.5	77.0
0°-40°	1729.2	95.5
0°-60°	1806.1	99.8
0°-90°	1810.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1810.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2549	
5°	2491	231
15°	1988	553
25°	1338	610
35°	492	336
45°	80	71
55°	5	6
65°	2	2
75°	1	1
85°	1	1
90°	0	



TEST NUMBER: P364675

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8040-F6LBXVM1-LI-BL86

CANDELA DISTRIBUTION (FULL):

0°	
0°	2549.4
2.5°	2548.1
5°	2491.4
7.5°	2404.1
10°	2274.5
12.5°	2145.6
15°	1988.0
17.5°	1827.6
20°	1651.6
22.5°	1497.5
25°	1337.8
27.5°	1183.6
30°	1003.5
32.5°	766.1
35°	491.9
37.5°	331.6
40°	219.7
42.5°	137.1
45°	79.8
47.5°	40.9
50°	19.1
52.5°	8.2
55°	4.8
57.5°	3.4
60°	2.7
62.5°	2.0
65°	2.0
67.5°	1.4
70°	1.4
72.5°	2.0
75°	1.4
77.5°	0.7
80°	0.7
82.5°	0.7
85°	0.7
87.5°	0.7
90°	0.0

(END OF REPORT)