

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P365448

Luminaire Tested: **FLD6BX30D010-FEU6B35-8030-F6LBXVM1-MW-BL85**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P365448  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-37)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD6BX30D010-FEU6B35-8030-F6LBXVM1-MW-BL85  
Description: VANDAL RESISTANT ENCLOSED BOTTOM LENS, MATTE WHITE REFLECTOR, BOTTOM LENS POLYCARBONATE, CLEAR 0.187", 3000LM  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2249.0 lumens  
Efficiency: N/A  
Efficacy: 83.3 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.95  
Luminous Opening: Circular (Dia: 0.71' x H: 0')  
CIE Type: Direct


Input Watts (W): 27  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P365448

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8030-F6LBXVM1-MW-BL85

### Luminous Intensity Polar Plot





TEST NUMBER: P365448

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8030-F6LBXVM1-MW-BL85

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	108	105	102	109	106	103	101	102	100	97		98	96	94		95	93	92	90
2	104	98	93	89	102	96	92	88	93	89	86		90	87	84		87	84	82	80
3	97	89	83	78	95	88	82	77	85	80	76		82	78	75		80	77	74	72
4	91	82	75	69	89	80	74	69	78	73	68		76	71	67		74	70	67	65
5	85	75	68	63	83	74	67	62	72	66	62		70	65	61		69	64	60	59
6	80	69	62	57	78	68	62	57	67	61	56		65	60	56		64	59	55	54
7	75	64	57	52	74	63	57	52	62	56	51		61	55	51		60	55	51	49
8	71	60	53	48	70	59	52	48	58	52	47		57	51	47		56	51	47	45
9	67	56	49	44	66	55	49	44	54	48	44		53	48	44		52	47	44	42
10	64	52	46	41	62	52	45	41	51	45	41		50	45	41		49	44	41	39

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	49788
5°	48686
10°	46176
15°	43281
20°	40385
25°	37143
30°	31822
35°	24226
40°	17797
45°	13482
50°	11040
55°	9710
60°	8675
65°	7607
70°	6501
75°	5066
80°	3398
85°	1536



TEST NUMBER: P365448

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8030-F6LBXVM1-MW-BL85

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	165.9	7.4
10°-20°	429.6	19.1
20°-30°	559.9	24.9
30°-40°	456.5	20.3
40°-50°	276.4	12.3
50°-60°	183.5	8.2
60°-70°	117.4	5.2
70°-80°	52.0	2.3
80°-90°	7.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1155.5	51.4
0°-40°	1612.0	71.7
0°-60°	2071.8	92.1
0°-90°	2249.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2249.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1823	
5°	1776	166
15°	1530	430
25°	1232	560
35°	726	456
45°	349	276
55°	204	184
65°	118	117
75°	48	52
85°	5	8
90°	0	



TEST NUMBER: P365448

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8030-F6LBXVM1-MW-BL85

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1822.7
2.5°	1808.9
5°	1775.6
7.5°	1725.6
10°	1664.8
12.5°	1598.1
15°	1530.5
17.5°	1462.8
20°	1389.3
22.5°	1318.7
25°	1232.4
27.5°	1132.4
30°	1008.9
32.5°	867.7
35°	726.5
37.5°	599.1
40°	499.1
42.5°	413.8
45°	349.0
47.5°	298.1
50°	259.8
52.5°	228.4
55°	203.9
57.5°	180.4
60°	158.8
62.5°	138.2
65°	117.7
67.5°	99.0
70°	81.4
72.5°	63.7
75°	48.0
77.5°	34.3
80°	21.6
82.5°	11.8
85°	4.9
87.5°	1.0
90°	0.0

(END OF REPORT)