

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P364679

Luminaire Tested: **FLD6BX20D010-FEU6B12-8040-F6LBXVM1-LI-BL89BW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P364679
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-42)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX20D010-FEU6B12-8040-F6LBXVM1-LI-BL89BW
Description: VANDAL RESISTANT ENCLOSED BOTTOM LENS, SPECULAR CLEAR REFLECTOR,
BOTTOM LENS ACRYLIC OPAL SMOOTH, CLEAR 0.125", 2000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1429.9 lumens
Efficiency: N/A
Efficacy: 70.4 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.36
Luminous Opening: Circular (Dia: 0.71' x H: 0')
CIE Type: Direct


Input Watts (W): 20.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P364679

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8040-F6LBXVM1-LI-BL89BW

Luminous Intensity Polar Plot





TEST NUMBER: P364679

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8040-F6LBXVM1-LI-BL89BW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	109	104	100	96	106	102	98	95	98	94	92		94	91	89		90	88	86	84
2	99	91	84	78	96	89	83	77	85	80	75		82	78	74		79	75	72	70
3	90	80	71	65	88	78	70	64	75	69	63		72	67	62		70	65	61	59
4	83	71	62	55	80	69	61	55	67	59	54		64	58	53		62	57	52	50
5	76	63	54	47	74	62	53	47	60	52	46		58	51	46		56	50	45	43
6	70	57	48	41	68	56	47	41	54	46	41		52	45	40		51	45	40	38
7	65	51	43	36	63	51	42	36	49	41	36		48	41	36		46	40	35	33
8	60	47	38	32	59	46	38	32	45	37	32		44	37	32		42	36	32	30
9	56	43	35	29	55	42	34	29	41	34	29		40	34	29		39	33	29	27
10	53	40	32	26	52	39	32	26	38	31	26		37	31	26		36	30	26	24

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	13942
5°	13937
10°	13791
15°	13707
20°	13668
25°	13523
30°	13430
35°	13298
40°	13104
45°	12964
50°	12761
55°	12515
60°	12123
65°	11608
70°	10854
75°	9657
80°	7739
85°	4795



TEST NUMBER: P364679

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8040-F6LBXVM1-LI-BL89BW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.1	3.4
10°-20°	137.1	9.6
20°-30°	207.2	14.5
30°-40°	249.1	17.4
40°-50°	258.7	18.1
50°-60°	234.6	16.4
60°-70°	177.6	12.4
70°-80°	96.9	6.8
80°-90°	20.7	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
<hr/>		
0°-30°	392.4	27.4
0°-40°	641.5	44.9
0°-60°	1134.8	79.4
0°-90°	1429.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1429.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	510	
5°	508	48
15°	485	137
25°	449	207
35°	399	249
45°	336	259
55°	263	235
65°	180	178
75°	92	97
85°	15	21
90°	0	



TEST NUMBER: P364679

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8040-F6LBXVM1-LI-BL89BW

CANDELA DISTRIBUTION (FULL):

0°	
0°	510.4
2.5°	508.3
5°	508.3
7.5°	504.2
10°	497.2
12.5°	493.8
15°	484.7
17.5°	477.8
20°	470.2
22.5°	461.2
25°	448.7
27.5°	437.6
30°	425.8
32.5°	412.6
35°	398.8
37.5°	382.8
40°	367.5
42.5°	352.3
45°	335.6
47.5°	318.3
50°	300.3
52.5°	282.2
55°	262.8
57.5°	242.7
60°	221.9
62.5°	201.1
65°	179.6
67.5°	158.1
70°	135.9
72.5°	113.7
75°	91.5
77.5°	70.0
80°	49.2
82.5°	31.2
85°	15.3
87.5°	4.9
90°	0.0

(END OF REPORT)