

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P365455

Luminaire Tested: **FLD6BX30D010-FEU6B35-8030-F6LBXVM1-MW-BTR81**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P365455
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-19)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX30D010-FEU6B35-8030-F6LBXVM1-MW-BTR81
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, MATTE WHITE REFLECTOR,
BOTTOM TRIM POLYCARBONATE, PATTERN 12 0.156", 3000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1543.0 lumens
Efficiency: N/A
Efficacy: 57.1 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.19
Luminous Opening: Circular (Dia: 0.44' x H: 0')
CIE Type: Direct


Input Watts (W): 27
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P365455

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8030-F6LBXVM1-MW-BTR81

Luminous Intensity Polar Plot





TEST NUMBER: P365455

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8030-F6LBXVM1-MW-BTR81

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	111	107	103	100	108	105	101	99	101	98	96		97	95	93		93	91	90	88
2	103	96	90	85	100	94	89	84	90	86	82		87	84	80		84	81	79	77
3	95	86	79	73	93	84	78	73	81	76	71		79	74	70		76	72	69	67
4	88	77	70	64	86	76	69	64	74	68	63		72	66	62		70	65	61	59
5	82	70	62	57	80	69	62	56	67	61	56		65	60	55		64	59	55	53
6	76	64	56	51	74	63	56	50	62	55	50		60	54	49		58	53	49	47
7	71	59	51	45	69	58	51	45	57	50	45		55	49	45		54	49	44	43
8	66	54	46	41	65	54	46	41	52	46	41		51	45	41		50	45	40	39
9	62	50	43	38	61	50	42	37	48	42	37		47	41	37		46	41	37	35
10	59	47	39	34	58	46	39	34	45	39	34		44	38	34		43	38	34	32

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	55871
5°	57069
10°	58514
15°	58205
20°	56691
25°	54054
30°	50252
35°	45759
40°	40771
45°	35239
50°	29374
55°	24355
60°	20349
65°	17264
70°	14780
75°	12200
80°	9690
85°	7230



TEST NUMBER: P365455

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8030-F6LBXVM1-MW-BTR81

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	76.2	4.9
10°-20°	220.6	14.3
20°-30°	313.7	20.3
30°-40°	326.2	21.1
40°-50°	268.1	17.4
50°-60°	177.0	11.5
60°-70°	102.6	6.6
70°-80°	47.8	3.1
80°-90°	10.9	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	610.4	39.6
0°-40°	936.6	60.7
0°-60°	1381.7	89.5
0°-90°	1543.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1543.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	780	
5°	794	76
15°	785	221
25°	684	314
35°	524	326
45°	348	268
55°	195	177
65°	102	103
75°	44	48
85°	9	11
90°	0	



TEST NUMBER: P365455

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8030-F6LBXVM1-MW-BTR81

CANDELA DISTRIBUTION (FULL):

0°	
0°	780.3
2.5°	785.2
5°	794.0
7.5°	802.8
10°	804.8
12.5°	796.0
15°	785.2
17.5°	768.5
20°	744.0
22.5°	716.6
25°	684.2
27.5°	649.9
30°	607.8
32.5°	566.6
35°	523.5
37.5°	478.4
40°	436.2
42.5°	391.1
45°	348.0
47.5°	304.9
50°	263.7
52.5°	229.4
55°	195.1
57.5°	166.6
60°	142.1
62.5°	120.6
65°	101.9
67.5°	86.3
70°	70.6
72.5°	56.9
75°	44.1
77.5°	33.3
80°	23.5
82.5°	15.7
85°	8.8
87.5°	3.9
90°	0.0

(END OF REPORT)