

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P365456

Luminaire Tested: **FLD6BX30D010-FEU6B35-8030-F6LBXVM1-MW-BTR82**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P365456
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-20)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX30D010-FEU6B35-8030-F6LBXVM1-MW-BTR82
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, MATTE WHITE REFLECTOR,
BOTTOM TRIM POLYCARBONATE, PATTERN 12 0.187", 3000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1582.0 lumens
Efficiency: N/A
Efficacy: 58.6 lumens/watt
Spacing Criteria (0/90/45): 1.02 / 1.02 / 1.09
Luminous Opening: Circular (Dia: 0.44' x H: 0')
CIE Type: Direct


Input Watts (W): 27
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P365456

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8030-F6LBXVM1-MW-BTR82

Luminous Intensity Polar Plot





TEST NUMBER: P365456

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8030-F6LBXVM1-MW-BTR82

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	111	107	104	100	108	105	102	99	101	98	96		97	95	93		93	92	90	88
2	103	96	90	86	100	94	89	85	91	86	83		88	84	81		85	82	79	77
3	95	86	79	74	93	85	78	73	82	77	72		79	75	71		77	73	70	68
4	88	78	71	65	86	77	70	64	74	68	64		72	67	63		70	66	62	60
5	82	71	63	58	80	70	63	57	68	62	57		66	61	56		64	59	56	54
6	77	65	57	52	75	64	57	51	62	56	51		61	55	50		59	54	50	48
7	72	60	52	46	70	59	52	46	57	51	46		56	50	46		55	50	45	44
8	67	55	47	42	66	54	47	42	53	47	42		52	46	42		51	46	41	40
9	63	51	44	39	62	51	43	39	49	43	38		48	42	38		47	42	38	36
10	60	48	40	36	58	47	40	36	46	40	35		45	39	35		44	39	35	34

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	68673
5°	67455
10°	65385
15°	63097
20°	60150
25°	56251
30°	51649
35°	46292
40°	40697
45°	34661
50°	28951
55°	23743
60°	19948
65°	16942
70°	14780
75°	12477
80°	10102
85°	8051



TEST NUMBER: P365456

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8030-F6LBXVM1-MW-BTR82

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	88.4	5.6
10°-20°	238.7	15.1
20°-30°	326.0	20.6
30°-40°	330.4	20.9
40°-50°	265.0	16.8
50°-60°	172.6	10.9
60°-70°	100.8	6.4
70°-80°	48.4	3.1
80°-90°	11.6	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	653.1	41.3
0°-40°	983.5	62.2
0°-60°	1421.1	89.8
0°-90°	1582.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1582.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	959	
5°	938	88
15°	851	239
25°	712	326
35°	530	330
45°	342	265
55°	190	173
65°	100	101
75°	45	48
85°	10	12
90°	0	



TEST NUMBER: P365456

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8030-F6LBXVM1-MW-BTR82

CANDELA DISTRIBUTION (FULL):

	0°
0°	959.1
2.5°	955.2
5°	938.5
7.5°	920.8
10°	899.3
12.5°	874.8
15°	851.2
17.5°	819.8
20°	789.4
22.5°	751.2
25°	712.0
27.5°	666.8
30°	624.7
32.5°	576.6
35°	529.6
37.5°	482.5
40°	435.4
42.5°	389.3
45°	342.3
47.5°	299.1
50°	259.9
52.5°	221.6
55°	190.2
57.5°	162.8
60°	139.3
62.5°	118.7
65°	100.0
67.5°	84.3
70°	70.6
72.5°	56.9
75°	45.1
77.5°	34.3
80°	24.5
82.5°	16.7
85°	9.8
87.5°	3.9
90°	0.0

(END OF REPORT)