

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P366126

Luminaire Tested: **FLD6BX20D010-FEU6B12-8040-F6LBXVM1-WMH-BTR87**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P366126
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-30)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX20D010-FEU6B12-8040-F6LBXVM1-WMH-BTR87
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, WARM HAZE REFLECTOR,
BOTTOM TRIM POLYCARBONATE, CLEAR 0.375", 2000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1512.0 lumens
Efficiency: N/A
Efficacy: 74.5 lumens/watt
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.8
Luminous Opening: Circular (Dia: 0.44' x H: 0')
CIE Type: Direct


Input Watts (W): 20.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P366126

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8040-F6LBXVM1-WMH-BTR87

Luminous Intensity Polar Plot





TEST NUMBER: P366126

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8040-F6LBXVM1-WMH-BTR87

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94
2	109	104	100	97	106	102	99	96	99	96	94	96	94	92	93	92	90	88
3	104	98	93	89	102	96	92	89	94	90	87	91	88	86	89	87	84	83
4	99	92	87	83	97	91	86	82	89	85	81	87	83	80	85	82	80	78
5	94	87	81	77	93	86	81	77	84	80	76	82	79	76	81	78	75	74
6	90	82	76	72	89	81	76	72	80	75	72	78	74	71	77	74	71	69
7	86	78	72	68	85	77	72	68	76	71	68	75	70	67	73	70	67	66
8	82	74	68	64	81	73	68	64	72	67	64	71	67	64	70	66	63	62
9	79	70	64	61	78	69	64	61	69	64	60	68	63	60	67	63	60	59
10	76	67	61	58	75	66	61	58	65	61	57	65	60	57	64	60	57	56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	156321
5°	153749
10°	146496
15°	133867
20°	114799
25°	92111
30°	64580
35°	29842
40°	9581
45°	3088
50°	1437
55°	1273
60°	1260
65°	1152
70°	1130
75°	1328
80°	1691
85°	2793



TEST NUMBER: P366126

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8040-F6LBXVM1-WMH-BTR87

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	200.6	13.3
10°-20°	499.7	33.1
20°-30°	524.8	34.7
30°-40°	232.9	15.4
40°-50°	30.1	2.0
50°-60°	9.4	0.6
60°-70°	6.6	0.4
70°-80°	4.9	0.3
80°-90°	3.0	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1225.2	81.0
0°-40°	1458.1	96.4
0°-60°	1497.5	99.0
0°-90°	1512.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1512.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2183	
5°	2139	201
15°	1806	500
25°	1166	525
35°	341	233
45°	30	30
55°	10	9
65°	7	7
75°	5	5
85°	3	3
90°	0	



TEST NUMBER: P366126

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8040-F6LBXVM1-WMH-BTR87

CANDELA DISTRIBUTION (FULL):

	0°
0°	2183.2
2.5°	2169.7
5°	2139.1
7.5°	2097.7
10°	2014.9
12.5°	1922.0
15°	1805.9
17.5°	1666.8
20°	1506.6
22.5°	1338.3
25°	1165.9
27.5°	972.5
30°	781.1
32.5°	574.1
35°	341.4
37.5°	181.9
40°	102.5
42.5°	56.3
45°	30.5
47.5°	15.6
50°	12.9
52.5°	11.5
55°	10.2
57.5°	9.5
60°	8.8
62.5°	7.5
65°	6.8
67.5°	5.4
70°	5.4
72.5°	4.8
75°	4.8
77.5°	4.1
80°	4.1
82.5°	3.4
85°	3.4
87.5°	2.0
90°	0.0

(END OF REPORT)