

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P364691

Luminaire Tested: **FLD6BX20D010-FEU6B12-8050-F6LBXVM1-LI-BL84**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P364691
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-43)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX20D010-FEU6B12-8050-F6LBXVM1-LI-BL84
Description: VANDAL RESISTANT ENCLOSED BOTTOM LENS, SPECULAR CLEAR REFLECTOR,
BOTTOM LENS POLYCARBONATE, CLEAR 0.125", 2000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1884.0 lumens
Efficiency: N/A
Efficacy: 92.8 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.82
Luminous Opening: Circular (Dia: 0.71' x H: 0')
CIE Type: Direct


Input Watts (W): 20.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P364691

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8050-F6LBXVM1-LI-BL84

Luminous Intensity Polar Plot





TEST NUMBER: P364691

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8050-F6LBXVM1-LI-BL84

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	109	104	100	97	106	102	99	96	99	96	94		96	94	92		93	91	90	88
3	103	97	93	89	101	96	92	88	93	90	87		91	88	85		89	86	84	83
4	99	91	86	82	97	90	85	82	88	84	81		86	83	80		84	81	79	77
5	94	86	80	76	92	85	80	76	83	79	75		82	78	75		80	77	74	73
6	90	81	75	71	88	80	75	71	79	74	71		77	73	70		76	73	70	68
7	85	77	71	67	84	76	71	67	75	70	66		74	69	66		72	69	66	64
8	82	72	67	63	80	72	67	63	71	66	63		70	65	62		69	65	62	61
9	78	69	63	59	77	68	63	59	67	62	59		66	62	59		66	62	59	57
10	74	65	60	56	74	65	60	56	64	59	56		63	59	56		63	58	56	54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	72487
5°	71107
10°	65667
15°	58515
20°	49974
25°	41969
30°	32948
35°	17073
40°	8155
45°	3210
50°	846
55°	238
60°	153
65°	136
70°	112
75°	148
80°	110
85°	219



TEST NUMBER: P364691

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8050-F6LBXVM1-LI-BL84

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	240.5	12.8
10°-20°	575.1	30.5
20°-30°	635.0	33.7
30°-40°	349.4	18.5
40°-50°	73.9	3.9
50°-60°	6.3	0.3
60°-70°	1.9	0.1
70°-80°	1.4	0.1
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1450.5	77.0
0°-40°	1799.9	95.5
0°-60°	1880.0	99.8
0°-90°	1884.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1884.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2654	
5°	2593	240
15°	2069	575
25°	1392	635
35°	512	349
45°	83	74
55°	5	6
65°	2	2
75°	1	1
85°	1	1
90°	0	



TEST NUMBER: P364691

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8050-F6LBXVM1-LI-BL84

CANDELA DISTRIBUTION (FULL):

	0°
0°	2653.7
2.5°	2652.2
5°	2593.3
7.5°	2502.4
10°	2367.5
12.5°	2233.3
15°	2069.2
17.5°	1902.4
20°	1719.2
22.5°	1558.7
25°	1392.5
27.5°	1232.0
30°	1044.6
32.5°	797.4
35°	512.0
37.5°	345.1
40°	228.7
42.5°	142.7
45°	83.1
47.5°	42.6
50°	19.9
52.5°	8.5
55°	5.0
57.5°	3.6
60°	2.8
62.5°	2.1
65°	2.1
67.5°	1.4
70°	1.4
72.5°	2.1
75°	1.4
77.5°	0.7
80°	0.7
82.5°	0.7
85°	0.7
87.5°	0.7
90°	0.0

(END OF REPORT)