

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P365458

Luminaire Tested: **FLD6BX30D010-FEU6B35-8030-F6LBXVM1-MW-BTR85**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P365458
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-16)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX30D010-FEU6B35-8030-F6LBXVM1-MW-BTR85
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, MATTE WHITE REFLECTOR,
BOTTOM TRIM POLYCARBONATE, CLEAR 0.187", 3000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1728.9 lumens
Efficiency: N/A
Efficacy: 64.0 lumens/watt
Spacing Criteria (0/90/45): 0.87 / 0.87 / 0.84
Luminous Opening: Circular (Dia: 0.44' x H: 0')
CIE Type: Direct


Input Watts (W): 27
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P365458

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8030-F6LBXVM1-MW-BTR85

Luminous Intensity Polar Plot





TEST NUMBER: P365458

CATALOG NUMBER: FLD6BX30D010-FEUGB35-8030-F6LBXVM1-MW-BTR85

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	103	110	107	104	101	102	100	98		99	97	95		95	94	92	91
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88	86	83	82
3	99	91	85	80	96	89	84	79	87	82	78		84	80	77		82	78	76	74
4	93	84	77	72	91	82	76	72	80	75	71		78	73	70		76	72	69	67
5	87	77	70	65	85	76	70	65	74	69	64		73	68	64		71	67	63	62
6	82	72	65	60	80	71	64	60	69	63	59		68	63	59		66	62	58	57
7	78	67	60	55	76	66	60	55	65	59	55		64	58	54		62	58	54	52
8	73	63	56	51	72	62	55	51	61	55	51		60	54	51		59	54	50	49
9	70	59	52	48	68	58	52	48	57	51	47		56	51	47		55	51	47	45
10	66	55	49	45	65	55	49	44	54	48	44		53	48	44		52	48	44	43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	120141
5°	117919
10°	112019
15°	104906
20°	95513
25°	79675
30°	57776
35°	39754
40°	29219
45°	23715
50°	20630
55°	18226
60°	15853
65°	13452
70°	10865
75°	7857
80°	5237
85°	5669



TEST NUMBER: P365458

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8030-F6LBXVM1-MW-BTR85

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	153.4	8.9
10°-20°	395.3	22.9
20°-30°	453.6	26.2
30°-40°	293.6	17.0
40°-50°	184.4	10.7
50°-60°	131.2	7.6
60°-70°	79.2	4.6
70°-80°	31.5	1.8
80°-90°	6.8	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1002.3	58.0
0°-40°	1295.9	75.0
0°-60°	1611.5	93.2
0°-90°	1728.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1728.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1678	
5°	1641	153
15°	1415	395
25°	1008	454
35°	455	294
45°	234	184
55°	146	131
65°	79	79
75°	28	31
85°	7	7
90°	0	



TEST NUMBER: P365458

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8030-F6LBXVM1-MW-BTR85

CANDELA DISTRIBUTION (FULL):

	0°
0°	1677.9
2.5°	1670.0
5°	1640.6
7.5°	1596.5
10°	1540.7
12.5°	1478.9
15°	1415.2
17.5°	1343.7
20°	1253.5
22.5°	1144.7
25°	1008.5
27.5°	856.6
30°	698.8
32.5°	565.5
35°	454.8
37.5°	373.4
40°	312.6
42.5°	268.5
45°	234.2
47.5°	207.8
50°	185.2
52.5°	165.6
55°	146.0
57.5°	128.4
60°	110.7
62.5°	95.1
65°	79.4
67.5°	64.7
70°	51.9
72.5°	39.2
75°	28.4
77.5°	19.6
80°	12.7
82.5°	7.8
85°	6.9
87.5°	3.9
90°	0.0

(END OF REPORT)