

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P366173

Luminaire Tested: **FLD6BX30D010-FEU6B35-8030-F6LBXVM1-WMH-BL89BW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P366173
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-46)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX30D010-FEU6B35-8030-F6LBXVM1-WMH-BL89BW
Description: VANDAL RESISTANT ENCLOSED BOTTOM LENS, WARM HAZE REFLECTOR, BOTTOM LENS ACRYLIC OPAL SMOOTH, CLEAR 0.125", 3000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1976.9 lumens
Efficiency: N/A
Efficacy: 73.2 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.36
Luminous Opening: Circular (Dia: 0.71' x H: 0')
CIE Type: Direct


Input Watts (W): 27
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P366173

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8030-F6LBXVM1-WMH-BL89BW

Luminous Intensity Polar Plot





TEST NUMBER: P366173

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8030-F6LBXVM1-WMH-BL89BW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | 0 | | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | | 50 | 30 | 10 | | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | | 106 | 106 | 106 | | 102 | 102 | 102 | 100 |
| 1 | 109 | 104 | 100 | 96 | 106 | 102 | 98 | 95 | 98 | 94 | 92 | | 94 | 91 | 89 | | 90 | 88 | 86 | 84 |
| 2 | 99 | 91 | 84 | 78 | 96 | 89 | 83 | 77 | 85 | 80 | 76 | | 82 | 78 | 74 | | 79 | 75 | 72 | 70 |
| 3 | 90 | 80 | 72 | 65 | 88 | 78 | 71 | 64 | 75 | 69 | 63 | | 72 | 67 | 62 | | 70 | 65 | 61 | 59 |
| 4 | 83 | 71 | 62 | 55 | 80 | 69 | 61 | 55 | 67 | 60 | 54 | | 64 | 58 | 53 | | 62 | 57 | 52 | 50 |
| 5 | 76 | 63 | 54 | 47 | 74 | 62 | 53 | 47 | 60 | 52 | 47 | | 58 | 51 | 46 | | 56 | 50 | 46 | 43 |
| 6 | 70 | 57 | 48 | 41 | 68 | 56 | 47 | 41 | 54 | 46 | 41 | | 52 | 45 | 40 | | 51 | 45 | 40 | 38 |
| 7 | 65 | 51 | 43 | 36 | 63 | 51 | 42 | 36 | 49 | 41 | 36 | | 48 | 41 | 36 | | 46 | 40 | 35 | 33 |
| 8 | 60 | 47 | 38 | 32 | 59 | 46 | 38 | 32 | 45 | 37 | 32 | | 44 | 37 | 32 | | 42 | 36 | 32 | 30 |
| 9 | 56 | 43 | 35 | 29 | 55 | 42 | 35 | 29 | 41 | 34 | 29 | | 40 | 34 | 29 | | 39 | 33 | 29 | 27 |
| 10 | 53 | 40 | 32 | 26 | 52 | 39 | 32 | 26 | 38 | 31 | 26 | | 37 | 31 | 26 | | 36 | 30 | 26 | 24 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|-------|
| | 0° |
| 0° | 19298 |
| 5° | 19265 |
| 10° | 19188 |
| 15° | 19066 |
| 20° | 18944 |
| 25° | 18783 |
| 30° | 18515 |
| 35° | 18330 |
| 40° | 18100 |
| 45° | 17905 |
| 50° | 17657 |
| 55° | 17316 |
| 60° | 16810 |
| 65° | 16087 |
| 70° | 15023 |
| 75° | 13340 |
| 80° | 10634 |
| 85° | 6456 |



TEST NUMBER: P366173

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8030-F6LBXVM1-WMH-BL89BW

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 66.7 | 3.4 |
| 10°-20° | 190.1 | 9.6 |
| 20°-30° | 286.7 | 14.5 |
| 30°-40° | 344.1 | 17.4 |
| 40°-50° | 357.4 | 18.1 |
| 50°-60° | 324.4 | 16.4 |
| 60°-70° | 246.1 | 12.4 |
| 70°-80° | 133.6 | 6.8 |
| 80°-90° | 27.8 | 1.4 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 543.5 | 27.5 |
| 0°-40° | 887.6 | 44.9 |
| 0°-60° | 1569.4 | 79.4 |
| 0°-90° | 1976.9 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 1976.9 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|-----|------|
| 0° | 706 | |
| 5° | 703 | 67 |
| 15° | 674 | 190 |
| 25° | 623 | 287 |
| 35° | 550 | 344 |
| 45° | 464 | 357 |
| 55° | 364 | 324 |
| 65° | 249 | 246 |
| 75° | 126 | 134 |
| 85° | 21 | 28 |
| 90° | 0 | |



TEST NUMBER: P366173

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8030-F6LBXVM1-WMH-BL89BW

CANDELA DISTRIBUTION (FULL):

| 0° | |
|-------|-------|
| 0° | 706.5 |
| 2.5° | 706.5 |
| 5° | 702.6 |
| 7.5° | 696.7 |
| 10° | 691.8 |
| 12.5° | 684.0 |
| 15° | 674.2 |
| 17.5° | 661.5 |
| 20° | 651.7 |
| 22.5° | 637.0 |
| 25° | 623.2 |
| 27.5° | 605.6 |
| 30° | 587.0 |
| 32.5° | 570.3 |
| 35° | 549.7 |
| 37.5° | 530.1 |
| 40° | 507.6 |
| 42.5° | 486.0 |
| 45° | 463.5 |
| 47.5° | 440.0 |
| 50° | 415.5 |
| 52.5° | 390.0 |
| 55° | 363.6 |
| 57.5° | 335.1 |
| 60° | 307.7 |
| 62.5° | 279.3 |
| 65° | 248.9 |
| 67.5° | 218.5 |
| 70° | 188.1 |
| 72.5° | 156.8 |
| 75° | 126.4 |
| 77.5° | 96.0 |
| 80° | 67.6 |
| 82.5° | 42.1 |
| 85° | 20.6 |
| 87.5° | 5.9 |
| 90° | 0.0 |

(END OF REPORT)