

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P364753

Luminaire Tested: **FLD6BX30D010-FEU6B35-8035-F6LBXVM1-LI-BTR81**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P364753
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-25)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX30D010-FEU6B35-8035-F6LBXVM1-LI-BTR81
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, SPECULAR CLEAR REFLECTOR, BOTTOM TRIM POLYCARBONATE, PATTERN 12 0.156", 3000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2205.0 lumens
Efficiency: N/A
Efficacy: 81.7 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.19
Luminous Opening: Circular (Dia: 0.44' x H: 0')
CIE Type: Direct


Input Watts (W): 27
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P364753

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8035-F6LBXVM1-LI-BTR81

Luminous Intensity Polar Plot





TEST NUMBER: P364753

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8035-F6LBXVM1-LI-BTR81

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	108	105	102	109	106	103	101	102	100	98		98	96	95		95	93	92	90
2	104	98	93	89	102	96	92	88	93	89	86		90	87	84		87	84	82	80
3	97	89	83	78	95	88	82	77	85	80	76		82	78	75		80	76	73	72
4	91	81	74	69	89	80	73	68	78	72	68		75	71	67		73	69	66	64
5	85	74	67	61	83	73	66	61	71	65	61		69	64	60		68	63	59	58
6	79	68	61	55	77	67	60	55	66	59	55		64	59	54		63	58	54	52
7	74	63	55	50	73	62	55	50	61	54	50		59	54	49		58	53	49	47
8	70	58	51	46	68	57	50	46	56	50	45		55	49	45		54	49	45	43
9	65	54	47	42	64	53	46	42	52	46	42		51	46	41		50	45	41	40
10	62	50	43	39	61	50	43	38	49	43	38		48	42	38		47	42	38	37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	81948
5°	87940
10°	94773
15°	97508
20°	96580
25°	91052
30°	82563
35°	71999
40°	60353
45°	48585
50°	37417
55°	27201
60°	18459
65°	12199
70°	7955
75°	6086
80°	5360
85°	6572



TEST NUMBER: P364753

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8035-F6LBXVM1-LI-BTR81

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	119.5	5.4
10°-20°	369.0	16.7
20°-30°	526.9	23.9
30°-40°	512.6	23.2
40°-50°	370.8	16.8
50°-60°	198.8	9.0
60°-70°	75.0	3.4
70°-80°	24.6	1.1
80°-90°	7.8	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1015.4	46.1
0°-40°	1528.1	69.3
0°-60°	2097.7	95.1
0°-90°	2205.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2205.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1144	
5°	1224	119
15°	1315	369
25°	1152	527
35°	824	513
45°	480	371
55°	218	199
65°	72	75
75°	22	25
85°	8	8
90°	0	



TEST NUMBER: P364753

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8035-F6LBXVM1-LI-BTR81

CANDELA DISTRIBUTION (FULL):

	0°
0°	1144.5
2.5°	1177.5
5°	1223.5
7.5°	1273.5
10°	1303.5
12.5°	1316.4
15°	1315.4
17.5°	1297.5
20°	1267.5
22.5°	1219.5
25°	1152.5
27.5°	1080.5
30°	998.6
32.5°	914.6
35°	823.7
37.5°	731.7
40°	645.7
42.5°	557.8
45°	479.8
47.5°	403.8
50°	335.9
52.5°	272.9
55°	217.9
57.5°	170.9
60°	128.9
62.5°	97.0
65°	72.0
67.5°	52.0
70°	38.0
72.5°	29.0
75°	22.0
77.5°	17.0
80°	13.0
82.5°	10.0
85°	8.0
87.5°	4.0
90°	0.0

(END OF REPORT)