

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P366146

Luminaire Tested: **FLD6BX20D010-FEU6B12-8050-F6LBXVM1-WMH-BTR89BV**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P366146
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-28)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX20D010-FEU6B12-8050-F6LBXVM1-WMH-BTR89BV
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, WARM HAZE REFLECTOR,
BOTTOM TRIM ACRYLIC, CLEAR 0.125", 2000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1651.1 lumens
Efficiency: N/A
Efficacy: 81.3 lumens/watt
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.8
Luminous Opening: Circular (Dia: 0.44' x H: 0')
CIE Type: Direct


Input Watts (W): 20.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P366146

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8050-F6LBXVM1-WMH-BTR89BV

Luminous Intensity Polar Plot





TEST NUMBER: P366146

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8050-F6LBXVM1-WMH-BTR89BV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94
2	109	104	100	97	106	102	99	96	99	96	94	96	94	92	93	92	90	88
3	104	98	93	89	102	96	92	89	94	90	87	91	88	86	89	87	85	83
4	99	92	87	83	97	91	86	82	89	85	81	87	83	80	85	82	80	78
5	94	87	81	77	93	86	81	77	84	80	76	82	79	76	81	78	75	74
6	90	82	76	72	89	81	76	72	80	75	72	78	74	71	77	74	71	69
7	86	78	72	68	85	77	72	68	76	71	68	75	70	67	74	70	67	66
8	82	74	68	64	81	73	68	64	72	67	64	71	67	64	70	66	63	62
9	79	70	65	61	78	70	64	61	69	64	61	68	63	60	67	63	60	59
10	76	67	61	58	75	66	61	58	65	61	57	65	60	57	64	60	57	56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	171014
5°	168706
10°	160594
15°	145987
20°	125710
25°	100493
30°	70467
35°	32779
40°	10356
45°	3240
50°	1426
55°	1336
60°	1217
65°	1084
70°	1193
75°	1383
80°	1773
85°	2958



TEST NUMBER: P366146

CATALOG NUMBER: FLD6BX20D010-FEUG6B12-8050-F6LBXVM1-WMH-BTR89BV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	219.7	13.3
10°-20°	546.1	33.1
20°-30°	574.1	34.8
30°-40°	254.7	15.4
40°-50°	31.9	1.9
50°-60°	9.5	0.6
60°-70°	6.7	0.4
70°-80°	5.3	0.3
80°-90°	3.1	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1339.9	81.2
0°-40°	1594.6	96.6
0°-60°	1636.0	99.1
0°-90°	1651.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1651.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2388	
5°	2347	220
15°	1969	546
25°	1272	574
35°	375	255
45°	32	32
55°	11	10
65°	6	7
75°	5	5
85°	4	3
90°	0	



TEST NUMBER: P366146

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8050-F6LBXVM1-WMH-BTR89BV

CANDELA DISTRIBUTION (FULL):

	0°
0°	2388.4
2.5°	2372.8
5°	2347.2
7.5°	2294.7
10°	2208.8
12.5°	2103.6
15°	1969.4
17.5°	1818.1
20°	1649.8
22.5°	1467.3
25°	1272.0
27.5°	1064.6
30°	852.3
32.5°	627.1
35°	375.0
37.5°	199.6
40°	110.8
42.5°	60.4
45°	32.0
47.5°	15.6
50°	12.8
52.5°	11.4
55°	10.7
57.5°	9.9
60°	8.5
62.5°	7.8
65°	6.4
67.5°	5.7
70°	5.7
72.5°	5.0
75°	5.0
77.5°	5.0
80°	4.3
82.5°	3.6
85°	3.6
87.5°	2.1
90°	0.0

(END OF REPORT)