

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P365468

Luminaire Tested: **FLD6BX30D010-FEU6B35-8035-F6LBXVM1-MW-BL87**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P365468
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-39)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX30D010-FEU6B35-8035-F6LBXVM1-MW-BL87
Description: VANDAL RESISTANT ENCLOSED BOTTOM LENS, MATTE WHITE REFLECTOR, BOTTOM LENS POLYCARBONATE, CLEAR 0.375", 3000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2173.0 lumens
Efficiency: N/A
Efficacy: 80.5 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.95
Luminous Opening: Circular (Dia: 0.71' x H: 0')
CIE Type: Direct


Input Watts (W): 27
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P365468

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8035-F6LBXVM1-MW-BL87

Luminous Intensity Polar Plot





TEST NUMBER: P365468

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8035-F6LBXVM1-MW-BL87

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	108	105	102	109	106	103	101	102	100	98	98	96	95	95	93	92	90
2	104	98	93	89	102	96	92	88	93	89	86	90	87	84	87	84	82	80
3	98	89	83	78	95	88	82	77	85	80	76	83	78	75	80	77	74	72
4	91	82	75	70	89	81	74	69	78	73	68	76	71	68	74	70	67	65
5	85	75	68	63	84	74	67	62	72	66	62	70	65	61	69	64	61	59
6	80	69	62	57	79	69	62	57	67	61	56	65	60	56	64	59	56	54
7	75	64	57	52	74	64	57	52	62	56	52	61	55	51	60	55	51	49
8	71	60	53	48	70	59	53	48	58	52	48	57	51	47	56	51	47	46
9	67	56	49	44	66	55	49	44	54	48	44	53	48	44	52	47	44	42
10	64	52	46	41	63	52	46	41	51	45	41	50	45	41	49	44	41	39

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	48425
5°	47293
10°	44900
15°	41988
20°	39295
25°	36040
30°	30749
35°	23539
40°	17112
45°	13057
50°	10581
55°	9286
60°	8249
65°	7174
70°	6070
75°	4749
80°	3146
85°	1254



TEST NUMBER: P365468

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8035-F6LBXVM1-MW-BL87

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	161.3	7.4
10°-20°	417.5	19.2
20°-30°	542.9	25.0
30°-40°	442.4	20.4
40°-50°	267.1	12.3
50°-60°	175.5	8.1
60°-70°	110.8	5.1
70°-80°	48.4	2.2
80°-90°	7.1	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1121.7	51.6
0°-40°	1564.1	72.0
0°-60°	2006.7	92.3
0°-90°	2173.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2173.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1773	
5°	1725	161
15°	1485	418
25°	1196	543
35°	706	442
45°	338	267
55°	195	175
65°	111	111
75°	45	48
85°	4	7
90°	0	



TEST NUMBER: P365468

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8035-F6LBXVM1-MW-BL87

CANDELA DISTRIBUTION (FULL):

0°	
0°	1772.8
2.5°	1756.8
5°	1724.8
7.5°	1678.8
10°	1618.8
12.5°	1556.8
15°	1484.8
17.5°	1419.8
20°	1351.8
22.5°	1278.8
25°	1195.8
27.5°	1096.8
30°	974.9
32.5°	838.9
35°	705.9
37.5°	583.9
40°	479.9
42.5°	401.9
45°	338.0
47.5°	288.0
50°	249.0
52.5°	219.0
55°	195.0
57.5°	172.0
60°	151.0
62.5°	131.0
65°	111.0
67.5°	93.0
70°	76.0
72.5°	60.0
75°	45.0
77.5°	31.0
80°	20.0
82.5°	11.0
85°	4.0
87.5°	1.0
90°	0.0

(END OF REPORT)