

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P365472

Luminaire Tested: **FLD6BX30D010-FEU6B35-8035-F6LBXVM1-MW-BTR80**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P365472
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-14)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX30D010-FEU6B35-8035-F6LBXVM1-MW-BTR80
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, MATTE WHITE REFLECTOR,
BOTTOM TRIM ACRYLIC, PATTERN 12 0.125", 3000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1734.0 lumens
Efficiency: N/A
Efficacy: 64.2 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.95
Luminous Opening: Circular (Dia: 0.44' x H: 0')
CIE Type: Direct


Input Watts (W): 27
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P365472

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8035-F6LBXVM1-MW-BTR80

Luminous Intensity Polar Plot





TEST NUMBER: P365472

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8035-F6LBXVM1-MW-BTR80

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	107	104	101	109	105	102	99	101	99	96	97	95	93	94	92	91	89
2	103	97	91	87	101	95	90	86	92	88	84	89	85	82	86	83	80	78
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	72	70
4	90	80	73	67	88	79	72	67	76	70	66	74	69	65	72	68	64	62
5	84	73	66	60	82	72	65	60	70	64	59	68	63	59	66	62	58	56
6	78	67	60	54	77	66	59	54	65	58	54	63	57	53	62	57	53	51
7	74	62	55	49	72	61	54	49	60	53	49	59	53	49	57	52	48	47
8	69	58	50	45	68	57	50	45	56	49	45	55	49	45	53	48	44	43
9	65	54	46	42	64	53	46	42	52	46	41	51	45	41	50	45	41	39
10	62	50	43	39	61	50	43	39	49	43	38	48	42	38	47	42	38	37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	93985
5°	92619
10°	88462
15°	81889
20°	74041
25°	65557
30°	56618
35°	47455
40°	39248
45°	32393
50°	27057
55°	23207
60°	20192
65°	17790
70°	15492
75°	13002
80°	10721
85°	8215



TEST NUMBER: P365472

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8035-F6LBXVM1-MW-BTR80

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	120.7	7.0
10°-20°	308.6	17.8
20°-30°	379.6	21.9
30°-40°	340.4	19.6
40°-50°	249.1	14.4
50°-60°	168.4	9.7
60°-70°	104.7	6.0
70°-80°	50.6	2.9
80°-90°	12.0	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	809.0	46.7
0°-40°	1149.3	66.3
0°-60°	1566.8	90.4
0°-90°	1734.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1734.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1313	
5°	1289	121
15°	1105	309
25°	830	380
35°	543	340
45°	320	249
55°	186	168
65°	105	105
75°	47	51
85°	10	12
90°	0	



TEST NUMBER: P365472

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8035-F6LBXVM1-MW-BTR80

CANDELA DISTRIBUTION (FULL):

	0°
0°	1312.6
2.5°	1306.6
5°	1288.6
7.5°	1258.7
10°	1216.7
12.5°	1166.7
15°	1104.7
17.5°	1039.7
20°	971.7
22.5°	901.8
25°	829.8
27.5°	754.8
30°	684.8
32.5°	612.8
35°	542.9
37.5°	479.9
40°	419.9
42.5°	365.9
45°	319.9
47.5°	278.9
50°	242.9
52.5°	213.9
55°	185.9
57.5°	163.0
60°	141.0
62.5°	122.0
65°	105.0
67.5°	89.0
70°	74.0
72.5°	60.0
75°	47.0
77.5°	35.0
80°	26.0
82.5°	17.0
85°	10.0
87.5°	4.0
90°	0.0

(END OF REPORT)