

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P366148

Luminaire Tested: **FLD6BX20D010-FEU6B12-8050-F6LBXVM1-WMH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P366148
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-11)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX20D010-FEU6B12-8050-F6LBXVM1-WMH
Description: VANDAL RESISTANT OPEN, WARM HAZE REFLECTOR, 2000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2031.0 lumens
Efficiency: N/A
Efficacy: 100.0 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.84
Luminous Opening: Circular (Dia: 0.71' x H: 0')
CIE Type: Direct


Input Watts (W): 20.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P366148

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8050-F6LBXVM1-WMH

Luminous Intensity Polar Plot





TEST NUMBER: P366148

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8050-F6LBXVM1-WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94
2	109	104	100	97	106	102	99	96	99	96	94	96	94	92	93	91	90	88
3	103	97	93	89	101	96	92	88	93	90	87	91	88	85	89	86	84	82
4	98	91	86	82	97	90	85	82	88	84	81	86	83	80	84	81	79	77
5	94	86	80	76	92	85	80	76	83	79	75	82	78	75	80	77	74	72
6	89	81	75	71	88	80	75	71	79	74	70	77	73	70	76	72	69	68
7	85	76	71	67	84	76	70	66	74	70	66	73	69	66	72	68	65	64
8	81	72	66	63	80	72	66	62	71	66	62	70	65	62	69	65	62	60
9	78	68	63	59	77	68	62	59	67	62	59	66	62	58	65	61	58	57
10	74	65	59	56	73	64	59	56	64	59	55	63	58	55	62	58	55	54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	73270
5°	72539
10°	68903
15°	62640
20°	54189
25°	45890
30°	35818
35°	19941
40°	8736
45°	3511
50°	965
55°	171
60°	115
65°	90
70°	56
75°	74
80°	0
85°	0



TEST NUMBER: P366148

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8050-F6LBXVM1-WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	247.3	12.2
10°-20°	614.6	30.3
20°-30°	690.4	34.0
30°-40°	390.6	19.2
40°-50°	80.5	4.0
50°-60°	5.8	0.3
60°-70°	1.2	0.1
70°-80°	0.5	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1552.3	76.4
0°-40°	1942.9	95.7
0°-60°	2029.3	99.9
0°-90°	2031.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2031.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2682	
5°	2646	247
15°	2215	615
25°	1523	690
35°	598	391
45°	91	81
55°	4	6
65°	1	1
75°	1	0
85°	0	0
90°	0	



TEST NUMBER: P366148

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8050-F6LBXVM1-WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	2682.4
2.5°	2671.0
5°	2645.5
7.5°	2582.2
10°	2484.2
12.5°	2362.1
15°	2215.1
17.5°	2048.2
20°	1864.2
22.5°	1688.1
25°	1522.6
27.5°	1339.4
30°	1135.6
32.5°	898.4
35°	598.0
37.5°	375.0
40°	245.0
42.5°	154.8
45°	90.9
47.5°	48.3
50°	22.7
52.5°	7.8
55°	3.6
57.5°	2.8
60°	2.1
62.5°	1.4
65°	1.4
67.5°	0.7
70°	0.7
72.5°	0.7
75°	0.7
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)