

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P364712

Luminaire Tested: **FLD6BX30D010-FEU6B35-8027-F6LBXVM1-LI-BL87**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P364712
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-43)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX30D010-FEU6B35-8027-F6LBXVM1-LI-BL87
Description: VANDAL RESISTANT ENCLOSED BOTTOM LENS, SPECULAR CLEAR REFLECTOR,
BOTTOM LENS POLYCARBONATE, CLEAR 0.375", 3000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2349.1 lumens
Efficiency: N/A
Efficacy: 87.0 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.82
Luminous Opening: Circular (Dia: 0.71' x H: 0')
CIE Type: Direct


Input Watts (W): 27
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P364712

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8027-F6LBXVM1-LI-BL87

Luminous Intensity Polar Plot





TEST NUMBER: P364712

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8027-F6LBXVM1-LI-BL87

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	109	104	100	97	106	102	99	96	99	96	94		96	94	92		93	91	90	88
3	103	97	93	89	101	96	92	88	93	90	87		91	88	85		89	86	84	83
4	99	91	86	82	97	90	85	82	88	84	81		86	83	80		84	81	79	77
5	94	86	80	76	92	85	80	76	83	79	75		82	78	75		80	77	74	73
6	90	81	75	71	88	80	75	71	79	74	71		77	73	70		76	73	70	68
7	85	77	71	67	84	76	71	67	75	70	66		74	69	66		72	69	66	64
8	82	72	67	63	80	72	67	63	71	66	62		70	65	62		69	65	62	61
9	78	69	63	59	77	68	63	59	67	62	59		66	62	59		66	62	59	57
10	74	65	60	56	73	65	60	56	64	59	56		63	59	56		63	58	56	54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	90375
5°	88659
10°	81873
15°	72959
20°	62308
25°	52327
30°	41079
35°	21285
40°	10166
45°	4002
50°	1054
55°	295
60°	191
65°	175
70°	144
75°	190
80°	142
85°	282



TEST NUMBER: P364712

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8027-F6LBXVM1-LI-BL87

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	299.8	12.8
10°-20°	717.0	30.5
20°-30°	791.7	33.7
30°-40°	435.6	18.5
40°-50°	92.1	3.9
50°-60°	7.8	0.3
60°-70°	2.4	0.1
70°-80°	1.8	0.1
80°-90°	0.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1808.5	77.0
0°-40°	2244.1	95.5
0°-60°	2344.0	99.8
0°-90°	2349.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2349.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3309	
5°	3233	300
15°	2580	717
25°	1736	792
35°	638	436
45°	104	92
55°	6	8
65°	3	2
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P364712

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8027-F6LBXVM1-LI-BL87

CANDELA DISTRIBUTION (FULL):

	0°
0°	3308.6
2.5°	3306.8
5°	3233.4
7.5°	3120.0
10°	2951.8
12.5°	2784.5
15°	2580.0
17.5°	2371.9
20°	2143.5
22.5°	1943.4
25°	1736.2
27.5°	1536.1
30°	1302.4
32.5°	994.3
35°	638.3
37.5°	430.3
40°	285.1
42.5°	178.0
45°	103.6
47.5°	53.1
50°	24.8
52.5°	10.6
55°	6.2
57.5°	4.4
60°	3.5
62.5°	2.7
65°	2.7
67.5°	1.8
70°	1.8
72.5°	2.7
75°	1.8
77.5°	0.9
80°	0.9
82.5°	0.9
85°	0.9
87.5°	0.9
90°	0.0

(END OF REPORT)