

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P364719

Luminaire Tested: **FLD6BX30D010-FEU6B35-8027-F6LBXVM1-LI-BTR84**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P364719
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-24)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX30D010-FEU6B35-8027-F6LBXVM1-LI-BTR84
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, SPECULAR CLEAR REFLECTOR, BOTTOM TRIM POLYCARBONATE, CLEAR 0.125", 3000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2121.0 lumens
Efficiency: N/A
Efficacy: 78.6 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.77
Luminous Opening: Circular (Dia: 0.44' x H: 0')
CIE Type: Direct


Input Watts (W): 27
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P364719

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8027-F6LBXVM1-LI-BTR84

Luminous Intensity Polar Plot





TEST NUMBER: P364719

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8027-F6LBXVM1-LI-BTR84

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	109	104	100	97	107	102	99	96	99	96	94		96	94	92		94	92	90	89
3	104	98	93	90	102	97	92	89	94	90	87		92	89	86		89	87	85	83
4	99	92	87	83	97	91	86	83	89	85	82		87	84	81		85	82	80	78
5	95	87	82	78	93	86	81	77	84	80	77		83	79	76		81	78	75	74
6	91	82	77	73	89	82	76	73	80	76	72		79	75	72		78	74	71	70
7	87	78	73	69	85	77	72	69	76	72	68		75	71	68		74	70	68	66
8	83	74	69	65	82	74	68	65	73	68	65		72	67	64		71	67	64	63
9	79	71	65	62	78	70	65	61	69	65	61		68	64	61		68	64	61	60
10	76	67	62	58	75	67	62	58	66	61	58		65	61	58		65	61	58	57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	238055
5°	232632
10°	214462
15°	189945
20°	160814
25°	127410
30°	89533
35°	37289
40°	12796
45°	3423
50°	1883
55°	1760
60°	1618
65°	1593
70°	1570
75°	1826
80°	2309
85°	3861



TEST NUMBER: P364719

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8027-F6LBXVM1-LI-BTR84

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	299.9	14.1
10°-20°	710.9	33.5
20°-30°	729.8	34.4
30°-40°	309.0	14.6
40°-50°	38.0	1.8
50°-60°	12.6	0.6
60°-70°	9.3	0.4
70°-80°	7.2	0.3
80°-90°	4.3	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1740.6	82.1
0°-40°	2049.6	96.6
0°-60°	2100.2	99.0
0°-90°	2121.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2121.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3325	
5°	3237	300
15°	2562	711
25°	1613	730
35°	427	309
45°	34	38
55°	14	13
65°	9	9
75°	7	7
85°	5	4
90°	0	



TEST NUMBER: P364719

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8027-F6LBXVM1-LI-BTR84

CANDELA DISTRIBUTION (FULL):

	0°
0°	3324.7
2.5°	3303.1
5°	3236.6
7.5°	3122.2
10°	2949.7
12.5°	2765.9
15°	2562.4
17.5°	2344.0
20°	2110.5
22.5°	1862.1
25°	1612.7
27.5°	1354.8
30°	1082.9
32.5°	763.2
35°	426.6
37.5°	244.7
40°	136.9
42.5°	72.2
45°	33.8
47.5°	19.7
50°	16.9
52.5°	15.0
55°	14.1
57.5°	13.1
60°	11.3
62.5°	10.3
65°	9.4
67.5°	8.4
70°	7.5
72.5°	7.5
75°	6.6
77.5°	6.6
80°	5.6
82.5°	5.6
85°	4.7
87.5°	2.8
90°	0.0

(END OF REPORT)