

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P364768

Luminaire Tested: **FLD6BX30D010-FEU6B35-8040-F6LBXVM1-LI-BL89BV**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P364768
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-41)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX30D010-FEU6B35-8040-F6LBXVM1-LI-BL89BV
Description: VANDAL RESISTANT ENCLOSED BOTTOM LENS, SPECULAR CLEAR REFLECTOR,
BOTTOM LENS ACRYLIC, CLEAR 0.125", 3000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2817.0 lumens
Efficiency: N/A
Efficacy: 104.3 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.82
Luminous Opening: Circular (Dia: 0.71' x H: 0')
CIE Type: Direct


Input Watts (W): 27
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P364768

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8040-F6LBXVM1-LI-BL89BV

Luminous Intensity Polar Plot





TEST NUMBER: P364768

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8040-F6LBXVM1-LI-BL89BV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	109	104	100	97	106	102	99	96	99	96	94		96	94	92		93	91	90	88
3	103	97	93	89	101	96	92	88	93	90	87		91	88	85		89	86	84	83
4	99	91	86	82	97	90	85	82	88	84	81		86	83	80		84	81	79	77
5	94	86	81	76	92	85	80	76	83	79	75		82	78	75		80	77	74	73
6	90	81	75	71	88	80	75	71	79	74	71		77	73	70		76	73	70	68
7	85	77	71	67	84	76	71	67	75	70	66		74	69	66		72	69	66	64
8	82	73	67	63	80	72	67	63	71	66	63		70	65	62		69	65	62	61
9	78	69	63	59	77	68	63	59	67	62	59		66	62	59		66	62	59	57
10	74	65	60	56	74	65	60	56	64	59	56		63	59	56		63	59	56	54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	109064
5°	106849
10°	98643
15°	87684
20°	74831
25°	62698
30°	49138
35°	25906
40°	12106
45°	4763
50°	1245
55°	338
60°	219
65°	194
70°	160
75°	211
80°	157
85°	313



TEST NUMBER: P364768

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8040-F6LBXVM1-LI-BL89BV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	360.6	12.8
10°-20°	861.1	30.6
20°-30°	947.2	33.6
30°-40°	522.8	18.6
40°-50°	110.3	3.9
50°-60°	9.0	0.3
60°-70°	2.7	0.1
70°-80°	2.2	0.1
80°-90°	1.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2168.9	77.0
0°-40°	2691.7	95.6
0°-60°	2811.0	99.8
0°-90°	2817.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2817.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3993	
5°	3897	361
15°	3101	861
25°	2080	947
35°	777	523
45°	123	110
55°	7	9
65°	3	3
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P364768

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8040-F6LBXVM1-LI-BL89BV

CANDELA DISTRIBUTION (FULL):

	0°
0°	3992.8
2.5°	3962.5
5°	3896.8
7.5°	3748.3
10°	3556.4
12.5°	3336.1
15°	3100.7
17.5°	2848.1
20°	2574.3
22.5°	2325.8
25°	2080.3
27.5°	1830.7
30°	1557.9
32.5°	1186.1
35°	776.9
37.5°	516.3
40°	339.5
42.5°	214.2
45°	123.3
47.5°	64.7
50°	29.3
52.5°	12.1
55°	7.1
57.5°	5.1
60°	4.0
62.5°	3.0
65°	3.0
67.5°	2.0
70°	2.0
72.5°	3.0
75°	2.0
77.5°	2.0
80°	1.0
82.5°	1.0
85°	1.0
87.5°	1.0
90°	0.0

(END OF REPORT)