

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P364774

Luminaire Tested: **FLD6BX30D010-FEU6B35-8040-F6LBXVM1-LI-BTR85**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P364774
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-24)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX30D010-FEU6B35-8040-F6LBXVM1-LI-BTR85
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, SPECULAR CLEAR REFLECTOR, BOTTOM TRIM POLYCARBONATE, CLEAR 0.187", 3000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2268.9 lumens
Efficiency: N/A
Efficacy: 84.0 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.77
Luminous Opening: Circular (Dia: 0.44' x H: 0')
CIE Type: Direct


Input Watts (W): 27
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P364774

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8040-F6LBXVM1-LI-BTR85

Luminous Intensity Polar Plot





TEST NUMBER: P364774

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8040-F6LBXVM1-LI-BTR85

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94
2	109	104	100	97	107	102	99	96	99	96	94	96	94	92	94	92	90	89
3	104	98	93	90	102	97	92	89	94	90	87	92	89	86	89	87	85	83
4	99	92	87	83	97	91	86	83	89	85	82	87	84	81	85	82	80	78
5	95	87	82	78	93	86	81	77	84	80	77	83	79	76	81	78	75	74
6	91	82	77	73	89	82	76	73	80	76	72	79	75	72	78	74	71	70
7	87	78	73	69	85	77	72	69	76	72	68	75	71	68	74	70	68	66
8	83	74	69	65	82	74	68	65	73	68	65	72	67	64	71	67	64	63
9	79	71	65	62	78	70	65	61	69	65	61	68	64	61	68	64	61	60
10	76	67	62	58	75	67	62	58	66	61	58	65	61	58	65	61	58	57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	254666
5°	248861
10°	229425
15°	203206
20°	172038
25°	136298
30°	95783
35°	39894
40°	13684
45°	3655
50°	2016
55°	1873
60°	1718
65°	1694
70°	1675
75°	1937
80°	2474
85°	4108



TEST NUMBER: P364774

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8040-F6LBXVM1-LI-BTR85

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	320.9	14.1
10°-20°	760.5	33.5
20°-30°	780.7	34.4
30°-40°	330.6	14.6
40°-50°	40.6	1.8
50°-60°	13.4	0.6
60°-70°	9.9	0.4
70°-80°	7.7	0.3
80°-90°	4.6	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1862.1	82.1
0°-40°	2192.7	96.6
0°-60°	2246.7	99.0
0°-90°	2268.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2268.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3557	
5°	3462	321
15°	2741	760
25°	1725	781
35°	456	331
45°	36	41
55°	15	13
65°	10	10
75°	7	8
85°	5	5
90°	0	



TEST NUMBER: P364774

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8040-F6LBXVM1-LI-BTR85

CANDELA DISTRIBUTION (FULL):

0°	
0°	3556.7
2.5°	3533.6
5°	3462.4
7.5°	3340.1
10°	3155.5
12.5°	2958.9
15°	2741.3
17.5°	2507.5
20°	2257.8
22.5°	1992.0
25°	1725.2
27.5°	1449.4
30°	1158.5
32.5°	816.5
35°	456.4
37.5°	261.8
40°	146.4
42.5°	77.2
45°	36.1
47.5°	21.1
50°	18.1
52.5°	16.0
55°	15.0
57.5°	14.0
60°	12.0
62.5°	11.0
65°	10.0
67.5°	9.0
70°	8.0
72.5°	8.0
75°	7.0
77.5°	7.0
80°	6.0
82.5°	6.0
85°	5.0
87.5°	3.0
90°	0.0

(END OF REPORT)