

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P364780

Luminaire Tested: **FLD6BX30D010-FEU6B35-8040-F6LBXVM1-LI**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P364780  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-10)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD6BX30D010-FEU6B35-8040-F6LBXVM1-LI  
Description: VANDAL RESISTANT OPEN, SPECULAR CLEAR REFLECTOR, 3000LM  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2962.0 lumens  
Efficiency: N/A  
Efficacy: 109.7 lumens/watt  
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.81  
Luminous Opening: Circular (Dia: 0.71' x H: 0')  
CIE Type: Direct


Input Watts (W): 27  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P364780

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8040-F6LBXVM1-LI

### Luminous Intensity Polar Plot





TEST NUMBER: P364780

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8040-F6LBXVM1-LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94
2	109	104	100	97	106	102	99	96	99	96	94	96	94	92	93	92	90	88
3	104	98	93	89	102	96	92	88	94	90	87	91	88	86	89	87	84	83
4	99	92	87	83	97	91	86	82	88	84	81	87	83	80	85	82	79	78
5	94	86	81	77	93	85	80	76	84	79	76	82	78	75	81	77	75	73
6	90	81	76	72	88	81	75	72	79	75	71	78	74	71	77	73	70	69
7	86	77	71	67	84	76	71	67	75	70	67	74	70	66	73	69	66	65
8	82	73	67	63	81	72	67	63	71	66	63	70	66	63	69	65	62	61
9	78	69	64	60	77	69	63	60	68	63	60	67	62	59	66	62	59	58
10	75	66	60	57	74	65	60	56	64	60	56	64	59	56	63	59	56	55

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	116961
5°	114277
10°	105646
15°	93422
20°	79638
25°	66246
30°	51383
35°	26690
40°	12395
45°	4686
50°	1033
55°	143
60°	55
65°	65
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P364780

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8040-F6LBXVM1-LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	386.2	13.0
10°-20°	918.3	31.0
20°-30°	1000.9	33.8
30°-40°	541.2	18.3
40°-50°	109.3	3.7
50°-60°	5.2	0.2
60°-70°	0.9	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2305.4	77.8
0°-40°	2846.6	96.1
0°-60°	2961.1	100.0
0°-90°	2962.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2962.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4282	
5°	4168	386
15°	3304	918
25°	2198	1001
35°	800	541
45°	121	109
55°	3	5
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P364780

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8040-F6LBXVM1-LI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	4281.9
2.5°	4253.6
5°	4167.7
7.5°	4013.0
10°	3808.9
12.5°	3565.3
15°	3303.6
17.5°	3032.8
20°	2739.7
22.5°	2463.8
25°	2198.0
27.5°	1931.2
30°	1629.1
32.5°	1225.8
35°	800.4
37.5°	534.6
40°	347.6
42.5°	214.2
45°	121.3
47.5°	60.6
50°	24.3
52.5°	6.1
55°	3.0
57.5°	2.0
60°	1.0
62.5°	1.0
65°	1.0
67.5°	1.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)