

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P365485

Luminaire Tested: **FLD6BX30D010-FEU6B35-8040-F6LBXVM1-MW-BL86**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P365485
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-38)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX30D010-FEU6B35-8040-F6LBXVM1-MW-BL86
Description: VANDAL RESISTANT ENCLOSED BOTTOM LENS, MATTE WHITE REFLECTOR, BOTTOM LENS POLYCARBONATE, CLEAR 0.250", 3000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2289.0 lumens
Efficiency: N/A
Efficacy: 84.8 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.95
Luminous Opening: Circular (Dia: 0.71' x H: 0')
CIE Type: Direct


Input Watts (W): 27
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P365485

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8040-F6LBXVM1-MW-BL86

Luminous Intensity Polar Plot





TEST NUMBER: P365485

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8040-F6LBXVM1-MW-BL86

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	108	105	102	109	106	103	101	102	100	97		98	96	95		95	93	92	90
2	104	98	93	89	102	96	92	88	93	89	86		90	87	84		87	84	82	80
3	97	89	83	78	95	88	82	77	85	80	76		83	78	75		80	77	74	72
4	91	82	75	70	89	80	74	69	78	73	68		76	71	67		74	70	67	65
5	85	75	68	63	84	74	67	62	72	66	62		70	65	61		69	64	61	59
6	80	69	62	57	78	68	62	57	67	61	56		65	60	56		64	59	55	54
7	75	64	57	52	74	64	57	52	62	56	52		61	55	51		60	55	51	49
8	71	60	53	48	70	59	52	48	58	52	47		57	51	47		56	51	47	45
9	67	56	49	44	66	55	49	44	54	48	44		53	48	44		52	47	44	42
10	64	52	46	41	62	52	45	41	51	45	41		50	45	41		49	44	41	39

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	50801
5°	49610
10°	47047
15°	44053
20°	41140
25°	37876
30°	32374
35°	24626
40°	18046
45°	13737
50°	11206
55°	9863
60°	8774
65°	7704
70°	6533
75°	5119
80°	3492
85°	1598



TEST NUMBER: P365485

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8040-F6LBXVM1-MW-BL86

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	169.1	7.4
10°-20°	437.9	19.1
20°-30°	570.1	24.9
30°-40°	465.3	20.3
40°-50°	281.3	12.3
50°-60°	186.3	8.1
60°-70°	118.6	5.2
70°-80°	52.5	2.3
80°-90°	8.0	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1177.1	51.4
0°-40°	1642.4	71.7
0°-60°	2110.0	92.2
0°-90°	2289.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2289.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1860	
5°	1809	169
15°	1558	438
25°	1257	570
35°	738	465
45°	356	281
55°	207	186
65°	119	119
75°	48	53
85°	5	8
90°	0	



TEST NUMBER: P365485

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8040-F6LBXVM1-MW-BL86

CANDELA DISTRIBUTION (FULL):

	0°
0°	1859.8
2.5°	1840.6
5°	1809.3
7.5°	1759.8
10°	1696.2
12.5°	1631.5
15°	1557.8
17.5°	1491.1
20°	1415.3
22.5°	1342.6
25°	1256.7
27.5°	1151.7
30°	1026.4
32.5°	886.0
35°	738.5
37.5°	613.2
40°	506.1
42.5°	421.3
45°	355.6
47.5°	304.1
50°	263.7
52.5°	232.4
55°	207.1
57.5°	182.9
60°	160.6
62.5°	139.4
65°	119.2
67.5°	100.0
70°	81.8
72.5°	64.7
75°	48.5
77.5°	34.3
80°	22.2
82.5°	12.1
85°	5.1
87.5°	1.0
90°	0.0

(END OF REPORT)