

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P364739

Luminaire Tested: **FLD6BX30D010-FEU6B35-8030-F6LBXVM1-LI-BTR86**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P364739  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-24)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD6BX30D010-FEU6B35-8030-F6LBXVM1-LI-BTR86  
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, SPECULAR CLEAR REFLECTOR, BOTTOM TRIM POLYCARBONATE, CLEAR 0.250", 3000LM  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2132.0 lumens  
Efficiency: N/A  
Efficacy: 79.0 lumens/watt  
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.77  
Luminous Opening: Circular (Dia: 0.44' x H: 0')  
CIE Type: Direct


Input Watts (W): 27  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P364739

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8030-F6LBXVM1-LI-BTR86

### Luminous Intensity Polar Plot





TEST NUMBER: P364739

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8030-F6LBXVM1-LI-BTR86

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	109	104	100	97	107	102	99	96	99	96	94		96	94	92		94	92	90	89
3	104	98	93	90	102	97	92	89	94	90	87		92	89	86		89	87	85	83
4	99	92	87	83	97	91	86	83	89	85	82		87	84	81		85	82	80	78
5	95	87	82	78	93	86	81	77	84	80	77		83	79	76		81	78	75	74
6	91	82	77	73	89	82	76	73	80	76	72		79	75	72		78	74	71	70
7	87	78	73	69	85	77	72	69	76	72	68		75	71	68		74	70	68	66
8	83	74	69	65	82	74	68	65	73	68	65		72	67	64		71	67	64	63
9	79	71	65	62	78	70	65	61	69	65	61		68	64	61		68	64	61	60
10	76	67	62	58	75	67	62	58	66	61	58		65	61	58		65	61	58	57

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	239293
5°	233839
10°	215575
15°	190931
20°	161652
25°	128065
30°	89996
35°	37481
40°	12861
45°	3433
50°	1894
55°	1760
60°	1618
65°	1593
70°	1570
75°	1826
80°	2350
85°	3861



TEST NUMBER: P364739

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8030-F6LBXVM1-LI-BTR86

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	301.5	14.1
10°-20°	714.6	33.5
20°-30°	733.6	34.4
30°-40°	310.6	14.6
40°-50°	38.2	1.8
50°-60°	12.6	0.6
60°-70°	9.3	0.4
70°-80°	7.2	0.3
80°-90°	4.4	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1749.6	82.1
0°-40°	2060.3	96.6
0°-60°	2111.1	99.0
0°-90°	2132.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2132.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3342	
5°	3253	301
15°	2576	715
25°	1621	734
35°	429	311
45°	34	38
55°	14	13
65°	9	9
75°	7	7
85°	5	4
90°	0	



TEST NUMBER: P364739

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8030-F6LBXVM1-LI-BTR86

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3342.0
2.5°	3320.3
5°	3253.4
7.5°	3138.4
10°	2965.0
12.5°	2780.3
15°	2575.7
17.5°	2356.1
20°	2121.5
22.5°	1871.7
25°	1621.0
27.5°	1361.9
30°	1088.5
32.5°	767.2
35°	428.8
37.5°	246.0
40°	137.6
42.5°	72.6
45°	33.9
47.5°	19.8
50°	17.0
52.5°	15.1
55°	14.1
57.5°	13.2
60°	11.3
62.5°	10.4
65°	9.4
67.5°	8.5
70°	7.5
72.5°	7.5
75°	6.6
77.5°	6.6
80°	5.7
82.5°	5.7
85°	4.7
87.5°	2.8
90°	0.0

(END OF REPORT)