

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P365497

Luminaire Tested: **FLD6BX30D010-FEU6B35-8040-F6LBXVM1-MW-BTR89BI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P365497
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-13)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX30D010-FEU6B35-8040-F6LBXVM1-MW-BTR89BI
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, MATTE WHITE REFLECTOR,
BOTTOM TRIM ACRYLIC, CLEAR RFI 0.125", 3000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1751.0 lumens
Efficiency: N/A
Efficacy: 64.9 lumens/watt
Spacing Criteria (0/90/45): 0.87 / 0.87 / 0.84
Luminous Opening: Circular (Dia: 0.44' x H: 0')
CIE Type: Direct


Input Watts (W): 27
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P365497

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8040-F6LBXVM1-MW-BTR89BI

Luminous Intensity Polar Plot





TEST NUMBER: P365497

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8040-F6LBXVM1-MW-BTR89BI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	103	109	106	104	101	102	100	98		99	97	95		95	94	92	90
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88	85	83	81
3	98	91	85	80	96	89	84	79	86	82	78		84	80	77		82	78	75	74
4	92	83	77	72	90	82	76	71	80	75	70		78	73	70		76	72	69	67
5	87	77	70	65	85	76	70	65	74	68	64		72	67	64		71	66	63	61
6	82	72	65	60	80	71	64	59	69	63	59		68	62	58		66	62	58	56
7	77	67	60	55	76	66	59	55	65	59	54		63	58	54		62	57	54	52
8	73	62	56	51	72	62	55	51	61	55	50		59	54	50		58	54	50	48
9	69	59	52	47	68	58	52	47	57	51	47		56	51	47		55	50	47	45
10	66	55	49	44	65	55	48	44	54	48	44		53	48	44		52	47	44	42

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	121050
5°	118752
10°	112775
15°	105617
20°	96405
25°	79912
30°	57983
35°	40104
40°	29658
45°	24252
50°	21276
55°	18925
60°	16497
65°	14045
70°	11221
75°	8106
80°	5814
85°	6654



TEST NUMBER: P365497

CATALOG NUMBER: FLD6BX30D010-FEUGB35-8040-F6LBXVM1-MW-BTR89BI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	154.4	8.8
10°-20°	398.4	22.8
20°-30°	455.7	26.0
30°-40°	295.4	16.9
40°-50°	188.4	10.8
50°-60°	135.7	7.7
60°-70°	82.5	4.7
70°-80°	32.8	1.9
80°-90°	7.7	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1008.5	57.6
0°-40°	1303.9	74.5
0°-60°	1628.0	93.0
0°-90°	1751.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1751.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1691	
5°	1652	154
15°	1425	398
25°	1012	456
35°	459	295
45°	240	188
55°	152	136
65°	83	82
75°	29	33
85°	8	8
90°	0	



TEST NUMBER: P365497

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8040-F6LBXVM1-MW-BTR89BI

CANDELA DISTRIBUTION (FULL):

0°	
0°	1690.6
2.5°	1680.5
5°	1652.2
7.5°	1605.7
10°	1551.1
12.5°	1490.5
15°	1424.8
17.5°	1355.1
20°	1265.2
22.5°	1150.0
25°	1011.5
27.5°	860.0
30°	701.3
32.5°	564.9
35°	458.8
37.5°	377.9
40°	317.3
42.5°	272.8
45°	239.5
47.5°	213.2
50°	191.0
52.5°	170.8
55°	151.6
57.5°	132.4
60°	115.2
62.5°	99.0
65°	82.9
67.5°	67.7
70°	53.6
72.5°	41.4
75°	29.3
77.5°	20.2
80°	14.1
82.5°	9.1
85°	8.1
87.5°	4.0
90°	0.0

(END OF REPORT)