

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P365462

Luminaire Tested: **FLD6BX30D010-FEU6B35-8030-F6LBXVM1-MW-BTR89BV**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P365462
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-12)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX30D010-FEU6B35-8030-F6LBXVM1-MW-BTR89BV
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, MATTE WHITE REFLECTOR,
BOTTOM TRIM ACRYLIC, CLEAR 0.125", 3000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1837.0 lumens
Efficiency: N/A
Efficacy: 68.0 lumens/watt
Spacing Criteria (0/90/45): 0.87 / 0.87 / 0.84
Luminous Opening: Circular (Dia: 0.44' x H: 0')
CIE Type: Direct


Input Watts (W): 27
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P365462

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8030-F6LBXVM1-MW-BTR89BV

Luminous Intensity Polar Plot





TEST NUMBER: P365462

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8030-F6LBXVM1-MW-BTR89BV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	103	110	107	104	101	102	100	98		99	97	95		95	94	92	91
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88	86	83	82
3	99	91	85	80	96	89	84	79	87	82	78		84	80	77		82	78	76	74
4	93	84	77	72	91	82	76	72	80	75	71		78	74	70		76	72	69	67
5	87	77	70	65	85	76	70	65	74	69	64		73	68	64		71	67	63	62
6	82	72	65	60	81	71	64	60	69	64	59		68	63	59		66	62	58	57
7	78	67	60	55	76	66	60	55	65	59	55		64	58	54		62	58	54	53
8	73	63	56	51	72	62	56	51	61	55	51		60	54	51		59	54	50	49
9	70	59	52	48	68	58	52	48	57	51	47		56	51	47		55	51	47	46
10	66	55	49	45	65	55	49	45	54	48	44		53	48	44		52	48	44	43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	128339
5°	125803
10°	119777
15°	111874
20°	101929
25°	85087
30°	61174
35°	42228
40°	30873
45°	25011
50°	21833
55°	19324
60°	16841
65°	14282
70°	11493
75°	8133
80°	5649
85°	6408



TEST NUMBER: P365462

CATALOG NUMBER: FLD6BX30D010-FEUGB35-8030-F6LBXVM1-MW-BTR89BV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	164.0	8.9
10°-20°	422.1	23.0
20°-30°	482.4	26.3
30°-40°	310.4	16.9
40°-50°	194.5	10.6
50°-60°	138.9	7.6
60°-70°	84.2	4.6
70°-80°	33.0	1.8
80°-90°	7.4	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1068.5	58.2
0°-40°	1378.9	75.1
0°-60°	1712.3	93.2
0°-90°	1837.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1837.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1792	
5°	1750	164
15°	1509	422
25°	1077	482
35°	483	310
45°	247	195
55°	155	139
65°	84	84
75°	29	33
85°	8	7
90°	0	



TEST NUMBER: P365462

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8030-F6LBXVM1-MW-BTR89BV

CANDELA DISTRIBUTION (FULL):

	0°
0°	1792.4
2.5°	1783.6
5°	1750.3
7.5°	1710.1
10°	1647.4
12.5°	1583.7
15°	1509.2
17.5°	1432.7
20°	1337.7
22.5°	1220.1
25°	1077.0
27.5°	904.5
30°	739.9
32.5°	594.9
35°	483.1
37.5°	394.9
40°	330.3
42.5°	282.2
45°	247.0
47.5°	219.5
50°	196.0
52.5°	175.4
55°	154.8
57.5°	135.2
60°	117.6
62.5°	100.9
65°	84.3
67.5°	69.6
70°	54.9
72.5°	41.2
75°	29.4
77.5°	20.6
80°	13.7
82.5°	8.8
85°	7.8
87.5°	3.9
90°	0.0

(END OF REPORT)