

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P366170

Luminaire Tested: **FLD6BX30D010-FEU6B35-8030-F6LBXVM1-WMH-BL87**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P366170
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-47)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX30D010-FEU6B35-8030-F6LBXVM1-WMH-BL87
Description: VANDAL RESISTANT ENCLOSED BOTTOM LENS, WARM HAZE REFLECTOR, BOTTOM LENS POLYCARBONATE, CLEAR 0.375", 3000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2425.0 lumens
Efficiency: N/A
Efficacy: 89.8 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.85
Luminous Opening: Circular (Dia: 0.71' x H: 0')
CIE Type: Direct


Input Watts (W): 27
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P366170

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8030-F6LBXVM1-WMH-BL87

Luminous Intensity Polar Plot





TEST NUMBER: P366170

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8030-F6LBXVM1-WMH-BL87

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	102	101	100	99	98	97	96	94
2	108	104	100	97	106	102	98	95	99	96	93	96	93	91	93	91	89	88
3	103	97	92	88	101	96	91	88	93	89	86	91	88	85	88	86	84	82
4	98	91	86	82	96	90	85	81	88	83	80	86	82	79	84	81	78	77
5	93	85	80	76	92	85	79	75	83	78	75	81	77	74	80	76	73	72
6	89	80	75	71	88	80	74	70	78	73	70	77	73	69	76	72	69	68
7	85	76	70	66	83	75	70	66	74	69	65	73	68	65	72	68	65	63
8	81	72	66	62	80	71	66	62	70	65	62	69	65	61	68	64	61	60
9	77	68	62	58	76	67	62	58	66	62	58	66	61	58	65	61	58	56
10	74	64	59	55	73	64	59	55	63	58	55	62	58	55	62	58	55	53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	85311
5°	84951
10°	80700
15°	73302
20°	63785
25°	54229
30°	42659
35°	24339
40°	10950
45°	4609
50°	1453
55°	443
60°	306
65°	239
70°	224
75°	296
80°	142
85°	282



TEST NUMBER: P366170

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8030-F6LBXVM1-WMH-BL87

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	289.8	12.0
10°-20°	721.1	29.7
20°-30°	817.1	33.7
30°-40°	473.7	19.5
40°-50°	105.0	4.3
50°-60°	11.5	0.5
60°-70°	3.8	0.2
70°-80°	2.5	0.1
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1827.9	75.4
0°-40°	2301.6	94.9
0°-60°	2418.1	99.7
0°-90°	2425.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2425.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3123	
5°	3098	290
15°	2592	721
25°	1799	817
35°	730	474
45°	119	105
55°	9	12
65°	4	4
75°	3	2
85°	1	1
90°	0	



TEST NUMBER: P366170

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8030-F6LBXVM1-WMH-BL87

CANDELA DISTRIBUTION (FULL):

0°	
0°	3123.2
2.5°	3125.9
5°	3098.2
7.5°	3030.6
10°	2909.5
12.5°	2762.4
15°	2592.1
17.5°	2412.7
20°	2194.3
22.5°	1997.3
25°	1799.3
27.5°	1588.4
30°	1352.5
32.5°	1074.0
35°	729.9
37.5°	469.0
40°	307.1
42.5°	200.7
45°	119.3
47.5°	66.6
50°	34.2
52.5°	15.7
55°	9.3
57.5°	7.4
60°	5.6
62.5°	4.6
65°	3.7
67.5°	2.8
70°	2.8
72.5°	2.8
75°	2.8
77.5°	1.9
80°	0.9
82.5°	0.9
85°	0.9
87.5°	0.0
90°	0.0

(END OF REPORT)