

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P366215

Luminaire Tested: **FLD6BX30D010-FEU6B35-8040-F6LBXVM1-WMH-BTR86**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P366215
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-30)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX30D010-FEU6B35-8040-F6LBXVM1-WMH-BTR86
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, WARM HAZE REFLECTOR,
BOTTOM TRIM POLYCARBONATE, CLEAR 0.250", 3000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2164.0 lumens
Efficiency: N/A
Efficacy: 80.1 lumens/watt
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.8
Luminous Opening: Circular (Dia: 0.44' x H: 0')
CIE Type: Direct


Input Watts (W): 27
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P366215

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8040-F6LBXVM1-WMH-BTR86

Luminous Intensity Polar Plot





TEST NUMBER: P366215

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8040-F6LBXVM1-WMH-BTR86

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	109	104	100	97	106	102	99	96	99	96	94		96	94	92		93	92	90	88
3	104	98	93	89	102	96	92	89	94	90	87		91	88	86		89	87	84	83
4	99	92	87	83	97	91	86	82	89	85	81		87	83	80		85	82	80	78
5	94	87	81	77	93	86	81	77	84	80	76		82	79	76		81	78	75	74
6	90	82	76	72	89	81	76	72	80	75	72		78	74	71		77	74	71	69
7	86	78	72	68	85	77	72	68	76	71	68		75	70	67		73	70	67	66
8	82	74	68	64	81	73	68	64	72	67	64		71	67	64		70	66	63	62
9	79	70	64	61	78	69	64	61	69	64	60		68	63	60		67	63	60	59
10	76	67	61	58	75	66	61	58	65	61	57		65	60	57		64	60	57	56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	223734
5°	220054
10°	209671
15°	191598
20°	164304
25°	131834
30°	92435
35°	42708
40°	13712
45°	4425
50°	2061
55°	1823
60°	1804
65°	1643
70°	1633
75°	1881
80°	2392
85°	4026



TEST NUMBER: P366215

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8040-F6LBXVM1-WMH-BTR86

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	287.1	13.3
10°-20°	715.2	33.1
20°-30°	751.1	34.7
30°-40°	333.3	15.4
40°-50°	43.1	2.0
50°-60°	13.5	0.6
60°-70°	9.5	0.4
70°-80°	6.9	0.3
80°-90°	4.2	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1753.5	81.0
0°-40°	2086.8	96.4
0°-60°	2143.4	99.0
0°-90°	2164.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2164.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3125	
5°	3062	287
15°	2585	715
25°	1669	751
35°	489	333
45°	44	43
55°	15	13
65°	10	9
75°	7	7
85°	5	4
90°	0	



TEST NUMBER: P366215

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8040-F6LBXVM1-WMH-BTR86

CANDELA DISTRIBUTION (FULL):

	0°
0°	3124.7
2.5°	3105.3
5°	3061.6
7.5°	3002.3
10°	2883.8
12.5°	2750.7
15°	2584.7
17.5°	2385.5
20°	2156.3
22.5°	1915.4
25°	1668.7
27.5°	1391.9
30°	1118.0
32.5°	821.7
35°	488.6
37.5°	260.3
40°	146.7
42.5°	80.6
45°	43.7
47.5°	22.3
50°	18.5
52.5°	16.5
55°	14.6
57.5°	13.6
60°	12.6
62.5°	10.7
65°	9.7
67.5°	7.8
70°	7.8
72.5°	6.8
75°	6.8
77.5°	5.8
80°	5.8
82.5°	4.9
85°	4.9
87.5°	2.9
90°	0.0

(END OF REPORT)