

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P366177

Luminaire Tested: **FLD6BX30D010-FEU6B35-8030-F6LBXVM1-WMH-BTR84**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P366177
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-30)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX30D010-FEU6B35-8030-F6LBXVM1-WMH-BTR84
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, WARM HAZE REFLECTOR,
BOTTOM TRIM POLYCARBONATE, CLEAR 0.125", 3000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2183.0 lumens
Efficiency: N/A
Efficacy: 80.9 lumens/watt
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.8
Luminous Opening: Circular (Dia: 0.44' x H: 0')
CIE Type: Direct


Input Watts (W): 27
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P366177

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8030-F6LBXVM1-WMH-BTR84

Luminous Intensity Polar Plot





TEST NUMBER: P366177

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8030-F6LBXVM1-WMH-BTR84

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94
2	109	104	100	97	106	102	99	96	99	96	94	96	94	92	93	92	90	88
3	104	98	93	89	102	96	92	89	94	90	87	91	88	86	89	87	84	83
4	99	92	87	83	97	91	86	82	89	85	81	87	83	80	85	82	80	78
5	94	87	81	77	93	86	81	77	84	80	76	82	79	76	81	78	75	74
6	90	82	76	72	89	81	76	72	80	75	72	78	74	71	77	74	71	69
7	86	78	72	68	85	77	72	68	76	71	68	75	70	67	73	70	67	66
8	82	74	68	64	81	73	68	64	72	67	64	71	67	64	70	66	63	62
9	79	70	64	61	78	69	64	61	69	64	60	68	63	60	67	63	60	59
10	76	67	61	58	75	66	61	58	65	61	57	65	60	57	64	60	57	56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	225696
5°	221980
10°	211510
15°	193273
20°	165744
25°	132995
30°	93245
35°	43084
40°	13833
45°	4466
50°	2072
55°	1835
60°	1819
65°	1660
70°	1633
75°	1909
80°	2433
85°	4026



TEST NUMBER: P366177

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8030-F6LBXVM1-WMH-BTR84

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	289.6	13.3
10°-20°	721.5	33.1
20°-30°	757.7	34.7
30°-40°	336.2	15.4
40°-50°	43.4	2.0
50°-60°	13.6	0.6
60°-70°	9.6	0.4
70°-80°	7.0	0.3
80°-90°	4.3	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1768.9	81.0
0°-40°	2105.1	96.4
0°-60°	2162.2	99.0
0°-90°	2183.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2183.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3152	
5°	3088	290
15°	2607	722
25°	1683	758
35°	493	336
45°	44	43
55°	15	14
65°	10	10
75°	7	7
85°	5	4
90°	0	



TEST NUMBER: P366177

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8030-F6LBXVM1-WMH-BTR84

CANDELA DISTRIBUTION (FULL):

	0°
0°	3152.1
2.5°	3132.5
5°	3088.4
7.5°	3028.7
10°	2909.1
12.5°	2774.9
15°	2607.3
17.5°	2406.5
20°	2175.2
22.5°	1932.2
25°	1683.4
27.5°	1404.1
30°	1127.8
32.5°	828.9
35°	492.9
37.5°	262.6
40°	148.0
42.5°	81.3
45°	44.1
47.5°	22.5
50°	18.6
52.5°	16.7
55°	14.7
57.5°	13.7
60°	12.7
62.5°	10.8
65°	9.8
67.5°	7.8
70°	7.8
72.5°	6.9
75°	6.9
77.5°	5.9
80°	5.9
82.5°	4.9
85°	4.9
87.5°	2.9
90°	0.0

(END OF REPORT)