

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P366219

Luminaire Tested: **FLD6BX30D010-FEU6B35-8040-F6LBXVM1-WMH-BTR94**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P366219  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-33)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD6BX30D010-FEU6B35-8040-F6LBXVM1-WMH-BTR94  
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, WARM HAZE REFLECTOR,  
BOTTOM TRIM GLASS, TEMPERED CLEAR 0.187", 3000LM  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2288.0 lumens  
Efficiency: N/A  
Efficacy: 84.7 lumens/watt  
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.8  
Luminous Opening: Circular (Dia: 0.44' x H: 0')  
CIE Type: Direct


Input Watts (W): 27  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P366219

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8040-F6LBXVM1-WMH-BTR94

### Luminous Intensity Polar Plot





TEST NUMBER: P366219

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8040-F6LBXVM1-WMH-BTR94

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	109	104	100	97	106	102	99	96	99	96	94		96	94	92		93	92	90	88
3	104	98	93	89	102	96	92	88	94	90	87		91	88	86		89	87	84	83
4	99	92	87	83	97	91	86	82	89	85	81		87	83	80		85	82	79	78
5	94	87	81	77	93	86	81	77	84	80	76		82	78	75		81	77	75	73
6	90	82	76	72	89	81	76	72	80	75	72		78	74	71		77	73	71	69
7	86	78	72	68	85	77	72	68	76	71	67		74	70	67		73	70	67	65
8	82	74	68	64	81	73	68	64	72	67	64		71	67	63		70	66	63	62
9	79	70	64	61	78	69	64	61	68	64	60		68	63	60		67	63	60	59
10	76	66	61	57	75	66	61	57	65	61	57		65	60	57		64	60	57	56

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	235298
5°	232632
10°	220853
15°	201123
20°	173089
25°	138668
30°	97834
35°	45313
40°	14731
45°	4709
50°	2250
55°	2022
60°	1876
65°	1711
70°	1696
75°	2241
80°	2515
85°	4190



TEST NUMBER: P366219

CATALOG NUMBER: FLD6BX30D010-FEUGB35-8040-F6LBXVM1-WMH-BTR94

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	302.4	13.2
10°-20°	752.5	32.9
20°-30°	794.1	34.7
30°-40°	355.3	15.5
40°-50°	46.5	2.0
50°-60°	14.3	0.6
60°-70°	10.1	0.4
70°-80°	8.0	0.4
80°-90°	4.7	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1849.0	80.8
0°-40°	2204.3	96.3
0°-60°	2265.2	99.0
0°-90°	2288.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2288.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3286	
5°	3237	302
15°	2713	752
25°	1755	794
35°	518	355
45°	46	47
55°	16	14
65°	10	10
75°	8	8
85°	5	5
90°	0	



TEST NUMBER: P366219

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8040-F6LBXVM1-WMH-BTR94

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	3286.2
2.5°	3264.9
5°	3236.6
7.5°	3156.8
10°	3037.6
12.5°	2895.1
15°	2713.2
17.5°	2511.1
20°	2271.6
22.5°	2028.1
25°	1755.2
27.5°	1479.4
30°	1183.3
32.5°	877.1
35°	518.4
37.5°	281.9
40°	157.6
42.5°	87.9
45°	46.5
47.5°	24.3
50°	20.2
52.5°	17.2
55°	16.2
57.5°	14.1
60°	13.1
62.5°	11.1
65°	10.1
67.5°	9.1
70°	8.1
72.5°	8.1
75°	8.1
77.5°	7.1
80°	6.1
82.5°	6.1
85°	5.1
87.5°	3.0
90°	0.0

(END OF REPORT)