

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P364761

Luminaire Tested: **FLD6BX30D010-FEU6B35-8035-F6LBXVM1-LI-BTR94**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P364761  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-27)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD6BX30D010-FEU6B35-8035-F6LBXVM1-LI-BTR94  
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, SPECULAR CLEAR REFLECTOR, BOTTOM TRIM GLASS, TEMPERED CLEAR 0.187", 3000LM  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2311.0 lumens  
Efficiency: N/A  
Efficacy: 85.6 lumens/watt  
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.77  
Luminous Opening: Circular (Dia: 0.44' x H: 0')  
CIE Type: Direct


Input Watts (W): 27  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P364761

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8035-F6LBXVM1-LI-BTR94

### Luminous Intensity Polar Plot





TEST NUMBER: P364761

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8035-F6LBXVM1-LI-BTR94

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94
2	109	104	100	97	107	102	99	96	99	96	94	96	94	92	94	92	90	88
3	104	98	93	90	102	96	92	89	94	90	87	92	89	86	89	87	85	83
4	99	92	87	83	97	91	86	83	89	85	82	87	84	81	85	82	80	78
5	95	87	82	78	93	86	81	77	84	80	77	83	79	76	81	78	75	74
6	91	82	77	73	89	82	76	73	80	76	72	79	75	72	77	74	71	70
7	87	78	73	69	85	77	72	68	76	72	68	75	71	68	74	70	67	66
8	83	74	69	65	82	74	68	65	73	68	64	72	67	64	71	67	64	63
9	79	71	65	61	78	70	65	61	69	64	61	68	64	61	67	64	61	59
10	76	67	62	58	75	67	62	58	66	61	58	65	61	58	65	61	58	57

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	258676
5°	251823
10°	232777
15°	207224
20°	174522
25°	139071
30°	97412
35°	41266
40°	14394
45°	3949
50°	2005
55°	1873
60°	1862
65°	1694
70°	1675
75°	2213
80°	2886
85°	4108



TEST NUMBER: P364761

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8035-F6LBXVM1-LI-BTR94

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	324.8	14.1
10°-20°	772.8	33.4
20°-30°	795.0	34.4
30°-40°	339.5	14.7
40°-50°	42.4	1.8
50°-60°	13.5	0.6
60°-70°	10.0	0.4
70°-80°	8.1	0.3
80°-90°	4.8	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1892.7	81.9
0°-40°	2232.2	96.6
0°-60°	2288.1	99.0
0°-90°	2311.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2311.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3613	
5°	3504	325
15°	2796	773
25°	1760	795
35°	472	340
45°	39	42
55°	15	14
65°	10	10
75°	8	8
85°	5	5
90°	0	



TEST NUMBER: P364761

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8035-F6LBXVM1-LI-BTR94

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	3612.7
2.5°	3583.6
5°	3503.6
7.5°	3375.6
10°	3201.6
12.5°	3007.5
15°	2795.5
17.5°	2543.5
20°	2290.4
22.5°	2030.4
25°	1760.3
27.5°	1475.3
30°	1178.2
32.5°	837.2
35°	472.1
37.5°	270.0
40°	154.0
42.5°	80.0
45°	39.0
47.5°	21.0
50°	18.0
52.5°	16.0
55°	15.0
57.5°	14.0
60°	13.0
62.5°	11.0
65°	10.0
67.5°	9.0
70°	8.0
72.5°	8.0
75°	8.0
77.5°	7.0
80°	7.0
82.5°	6.0
85°	5.0
87.5°	3.0
90°	0.0

(END OF REPORT)