

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P365511

Luminaire Tested: **FLD6BX30D010-FEU6B35-8050-F6LBXVM1-MW-BTR84**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P365511
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-15)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX30D010-FEU6B35-8050-F6LBXVM1-MW-BTR84
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, MATTE WHITE REFLECTOR,
BOTTOM TRIM POLYCARBONATE, CLEAR 0.125", 3000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1839.0 lumens
Efficiency: N/A
Efficacy: 68.1 lumens/watt
Spacing Criteria (0/90/45): 0.87 / 0.87 / 0.84
Luminous Opening: Circular (Dia: 0.44' x H: 0')
CIE Type: Direct


Input Watts (W): 27
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P365511

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8050-F6LBXVM1-MW-BTR84

Luminous Intensity Polar Plot





TEST NUMBER: P365511

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8050-F6LBXVM1-MW-BTR84

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | 0 |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |
| 1 | 112 | 109 | 106 | 103 | 110 | 107 | 104 | 101 | 102 | 100 | 98 | 99 | 97 | 95 | 95 | 94 | 93 | 91 |
| 2 | 105 | 99 | 94 | 90 | 103 | 97 | 93 | 89 | 94 | 90 | 87 | 91 | 88 | 85 | 88 | 86 | 84 | 82 |
| 3 | 99 | 91 | 85 | 80 | 96 | 89 | 84 | 80 | 87 | 82 | 78 | 84 | 80 | 77 | 82 | 79 | 76 | 74 |
| 4 | 93 | 84 | 77 | 72 | 91 | 82 | 76 | 72 | 80 | 75 | 71 | 78 | 74 | 70 | 76 | 72 | 69 | 67 |
| 5 | 87 | 77 | 71 | 65 | 85 | 76 | 70 | 65 | 74 | 69 | 65 | 73 | 68 | 64 | 71 | 67 | 63 | 62 |
| 6 | 82 | 72 | 65 | 60 | 81 | 71 | 64 | 60 | 69 | 64 | 59 | 68 | 63 | 59 | 67 | 62 | 58 | 57 |
| 7 | 78 | 67 | 60 | 55 | 76 | 66 | 60 | 55 | 65 | 59 | 55 | 64 | 58 | 54 | 62 | 58 | 54 | 53 |
| 8 | 73 | 63 | 56 | 51 | 72 | 62 | 56 | 51 | 61 | 55 | 51 | 60 | 55 | 51 | 59 | 54 | 50 | 49 |
| 9 | 70 | 59 | 52 | 48 | 68 | 58 | 52 | 48 | 57 | 52 | 47 | 56 | 51 | 47 | 55 | 51 | 47 | 46 |
| 10 | 66 | 55 | 49 | 45 | 65 | 55 | 49 | 45 | 54 | 48 | 44 | 53 | 48 | 44 | 52 | 48 | 44 | 43 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|--------|
| | 0° |
| 0° | 129163 |
| 5° | 126831 |
| 10° | 119944 |
| 15° | 112163 |
| 20° | 101967 |
| 25° | 84874 |
| 30° | 61265 |
| 35° | 42341 |
| 40° | 30957 |
| 45° | 25153 |
| 50° | 21900 |
| 55° | 19249 |
| 60° | 16741 |
| 65° | 14198 |
| 70° | 11493 |
| 75° | 8023 |
| 80° | 5113 |
| 85° | 5915 |



TEST NUMBER: P365511

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8050-F6LBXVM1-MW-BTR84

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 164.7 | 9.0 |
| 10°-20° | 422.8 | 23.0 |
| 20°-30° | 482.9 | 26.3 |
| 30°-40° | 311.5 | 16.9 |
| 40°-50° | 195.6 | 10.6 |
| 50°-60° | 138.7 | 7.5 |
| 60°-70° | 83.6 | 4.5 |
| 70°-80° | 32.3 | 1.8 |
| 80°-90° | 7.0 | 0.4 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 1070.4 | 58.2 |
| 0°-40° | 1381.8 | 75.1 |
| 0°-60° | 1716.1 | 93.3 |
| 0°-90° | 1839.0 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 1839.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 1804 | |
| 5° | 1765 | 165 |
| 15° | 1513 | 423 |
| 25° | 1074 | 483 |
| 35° | 484 | 311 |
| 45° | 248 | 196 |
| 55° | 154 | 139 |
| 65° | 84 | 84 |
| 75° | 29 | 32 |
| 85° | 7 | 7 |
| 90° | 0 | |



TEST NUMBER: P365511

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8050-F6LBXVM1-MW-BTR84

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|--------|
| 0° | 1803.9 |
| 2.5° | 1793.6 |
| 5° | 1764.6 |
| 7.5° | 1714.9 |
| 10° | 1649.7 |
| 12.5° | 1585.5 |
| 15° | 1513.1 |
| 17.5° | 1435.5 |
| 20° | 1338.2 |
| 22.5° | 1220.2 |
| 25° | 1074.3 |
| 27.5° | 909.7 |
| 30° | 741.0 |
| 32.5° | 599.2 |
| 35° | 484.4 |
| 37.5° | 395.4 |
| 40° | 331.2 |
| 42.5° | 284.6 |
| 45° | 248.4 |
| 47.5° | 220.4 |
| 50° | 196.6 |
| 52.5° | 174.9 |
| 55° | 154.2 |
| 57.5° | 135.6 |
| 60° | 116.9 |
| 62.5° | 100.4 |
| 65° | 83.8 |
| 67.5° | 68.3 |
| 70° | 54.9 |
| 72.5° | 40.4 |
| 75° | 29.0 |
| 77.5° | 19.7 |
| 80° | 12.4 |
| 82.5° | 8.3 |
| 85° | 7.2 |
| 87.5° | 4.1 |
| 90° | 0.0 |

(END OF REPORT)