

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P366191

Luminaire Tested: **FLD6BX30D010-FEU6B35-8035-F6LBXVM1-WMH-BL89BW**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P366191  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-46)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD6BX30D010-FEU6B35-8035-F6LBXVM1-WMH-BL89BW  
Description: VANDAL RESISTANT ENCLOSED BOTTOM LENS, WARM HAZE REFLECTOR, BOTTOM LENS ACRYLIC OPAL SMOOTH, CLEAR 0.125", 3000LM  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2017.0 lumens  
Efficiency: N/A  
Efficacy: 74.7 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.36  
Luminous Opening: Circular (Dia: 0.71' x H: 0')  
CIE Type: Direct


Input Watts (W): 27  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P366191

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8035-F6LBXVM1-WMH-BL89BW

### Luminous Intensity Polar Plot





TEST NUMBER: P366191

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8035-F6LBXVM1-WMH-BL89BW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	109	104	100	96	106	102	98	95	98	94	92		94	91	89		90	88	86	84
2	99	91	84	78	96	89	83	77	85	80	76		82	78	74		79	75	72	70
3	90	80	72	65	88	78	71	64	75	69	63		72	67	62		70	65	61	59
4	83	71	62	55	80	69	61	55	67	60	54		64	58	53		62	57	52	50
5	76	63	54	47	74	62	53	47	60	52	47		58	51	46		56	50	46	43
6	70	57	48	41	68	56	47	41	54	46	41		52	45	40		51	45	40	38
7	65	51	43	36	63	51	42	36	49	41	36		48	41	36		46	40	35	33
8	60	47	38	32	59	46	38	32	45	37	32		44	37	32		42	36	32	30
9	56	43	35	29	55	42	35	29	41	34	29		40	34	29		39	33	29	27
10	53	40	32	26	52	39	32	26	38	31	26		37	31	26		36	30	26	24

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	19689
5°	19654
10°	19577
15°	19450
20°	19325
25°	19165
30°	18890
35°	18704
40°	18467
45°	18268
50°	18014
55°	17663
60°	17149
65°	16410
70°	15334
75°	13614
80°	10854
85°	6582



TEST NUMBER: P366191

CATALOG NUMBER: FLD6BX30D010-FEUG6B35-8035-F6LBXVM1-WMH-BL89BW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	68.0	3.4
10°-20°	194.0	9.6
20°-30°	292.5	14.5
30°-40°	351.1	17.4
40°-50°	364.7	18.1
50°-60°	330.9	16.4
60°-70°	251.0	12.4
70°-80°	136.4	6.8
80°-90°	28.4	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	554.5	27.5
0°-40°	905.6	44.9
0°-60°	1601.2	79.4
0°-90°	2017.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2017.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	721	
5°	717	68
15°	688	194
25°	636	293
35°	561	351
45°	473	365
55°	371	331
65°	254	251
75°	129	136
85°	21	28
90°	0	



TEST NUMBER: P366191

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8035-F6LBXVM1-WMH-BL89BW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	720.8
2.5°	720.8
5°	716.8
7.5°	710.8
10°	705.8
12.5°	697.8
15°	687.8
17.5°	674.8
20°	664.8
22.5°	649.8
25°	635.9
27.5°	617.9
30°	598.9
32.5°	581.9
35°	560.9
37.5°	540.9
40°	517.9
42.5°	495.9
45°	472.9
47.5°	448.9
50°	423.9
52.5°	397.9
55°	370.9
57.5°	341.9
60°	313.9
62.5°	284.9
65°	253.9
67.5°	222.9
70°	192.0
72.5°	160.0
75°	129.0
77.5°	98.0
80°	69.0
82.5°	43.0
85°	21.0
87.5°	6.0
90°	0.0

(END OF REPORT)