

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P366193

Luminaire Tested: **FLD6BX30D010-FEU6B35-8035-F6LBXVM1-WMH-BTR81**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P366193
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-31)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX30D010-FEU6B35-8035-F6LBXVM1-WMH-BTR81
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, WARM HAZE REFLECTOR,
BOTTOM TRIM POLYCARBONATE, PATTERN 12 0.156", 3000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2144.0 lumens
Efficiency: N/A
Efficacy: 79.4 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.19
Luminous Opening: Circular (Dia: 0.44' x H: 0')
CIE Type: Direct


Input Watts (W): 27
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P366193

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8035-F6LBXVM1-WMH-BTR81

Luminous Intensity Polar Plot





TEST NUMBER: P366193

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8035-F6LBXVM1-WMH-BTR81

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	108	105	102	109	106	103	101	102	100	98		98	96	95		95	93	92	90
2	104	98	93	89	102	96	92	88	93	89	86		90	87	84		87	84	82	80
3	97	89	83	78	95	88	82	77	85	80	76		82	78	74		80	76	73	71
4	91	81	74	69	89	80	73	68	78	72	67		75	71	67		73	69	66	64
5	85	74	67	61	83	73	66	61	71	65	60		69	64	60		68	63	59	57
6	79	68	61	55	77	67	60	55	65	59	55		64	58	54		62	58	54	52
7	74	63	55	50	72	62	55	50	60	54	49		59	53	49		58	53	49	47
8	69	58	51	46	68	57	50	45	56	50	45		55	49	45		54	49	45	43
9	65	54	47	42	64	53	46	42	52	46	41		51	45	41		50	45	41	39
10	62	50	43	38	60	49	43	38	49	42	38		48	42	38		47	42	38	36

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	80710
5°	86265
10°	92352
15°	94379
20°	92366
25°	87473
30°	79628
35°	69849
40°	58989
45°	47704
50°	36760
55°	26839
60°	18473
65°	12199
70°	7955
75°	5810
80°	4948
85°	5751



TEST NUMBER: P366193

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8035-F6LBXVM1-WMH-BTR81

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	116.8	5.4
10°-20°	356.5	16.6
20°-30°	505.2	23.6
30°-40°	498.2	23.2
40°-50°	365.2	17.0
50°-60°	195.8	9.1
60°-70°	75.2	3.5
70°-80°	24.0	1.1
80°-90°	7.1	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	978.5	45.6
0°-40°	1476.7	68.9
0°-60°	2037.7	95.0
0°-90°	2144.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2144.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1127	
5°	1200	117
15°	1273	357
25°	1107	505
35°	799	498
45°	471	365
55°	215	196
65°	72	75
75°	21	24
85°	7	7
90°	0	



TEST NUMBER: P366193

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8035-F6LBXVM1-WMH-BTR81

CANDELA DISTRIBUTION (FULL):

0°	
0°	1127.2
2.5°	1153.2
5°	1200.2
7.5°	1244.2
10°	1270.2
12.5°	1279.2
15°	1273.2
17.5°	1249.2
20°	1212.2
22.5°	1165.2
25°	1107.2
27.5°	1035.1
30°	963.1
32.5°	885.1
35°	799.1
37.5°	717.1
40°	631.1
42.5°	552.1
45°	471.1
47.5°	399.1
50°	330.0
52.5°	268.0
55°	215.0
57.5°	168.0
60°	129.0
62.5°	97.0
65°	72.0
67.5°	53.0
70°	38.0
72.5°	29.0
75°	21.0
77.5°	16.0
80°	12.0
82.5°	9.0
85°	7.0
87.5°	4.0
90°	0.0

(END OF REPORT)