

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P236150

Luminaire Tested: **FLD6BX40D010 EU6B3/58040 F6LBXVM1LI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P236150
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX40D010 EU6B3/58040 F6LBXVM1LI
Description: FAILSAFE 6 INCH RECESSED LED DOWNLIGHT
6" LED Vandal Resistant, Medium (50° Beam), Specular Clear, Bottom open
Light Source: (1) 4000K CCT, 80 CRI LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3872.0 lumens
Efficiency: N/A
Efficacy: 92.6 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.91
Luminous Opening: Circular (Dia: 0.46' x H: 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P236150

CATALOG NUMBER: FLD6BX40D010 EU6B3/58040 F6LBXVM1LI

Luminous Intensity Polar Plot





TEST NUMBER: P236150

CATALOG NUMBER: FLD6BX40D010 EU6B3/58040 F6LBXVM1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	108	105	111	108	106	104	104	102	101	100	99	98	97	96	95	93
2	107	102	98	94	105	100	97	93	97	94	91	94	92	89	91	89	87	86
3	102	95	90	85	100	93	89	85	91	87	83	88	85	82	86	83	81	79
4	96	88	82	78	94	87	82	77	85	80	77	83	79	76	81	78	75	73
5	91	82	76	72	89	81	76	71	79	74	71	78	73	70	76	72	69	68
6	86	77	71	66	85	76	70	66	74	69	65	73	68	65	72	68	64	63
7	82	72	66	61	80	71	65	61	70	65	61	69	64	60	68	63	60	59
8	77	68	61	57	76	67	61	57	66	60	57	65	60	56	64	59	56	55
9	74	64	57	53	72	63	57	53	62	57	53	61	56	53	60	56	53	51
10	70	60	54	50	69	59	54	50	59	53	50	58	53	49	57	53	49	48

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	263233
5°	259634
10°	247612
15°	231325
20°	216066
25°	195886
30°	160227
35°	109606
40°	65262
45°	35356
50°	17457
55°	10669
60°	7137
65°	4832
70°	2976
75°	1966
80°	2931
85°	0



TEST NUMBER: P236150

CATALOG NUMBER: FLD6BX40D010 EU6B3/58040 F6LBXVM1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	370.7	9.6
10°-20°	961.8	24.8
20°-30°	1225.5	31.7
30°-40°	866.1	22.4
40°-50°	316.2	8.2
50°-60°	87.6	2.3
60°-70°	31.8	0.8
70°-80°	11.3	0.3
80°-90°	1.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2558.0	66.1
0°-40°	3424.0	88.4
0°-60°	3827.8	98.9
0°-90°	3872.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3872.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4035	
5°	3964	371
15°	3425	962
25°	2721	1225
35°	1376	866
45°	383	316
55°	94	88
65°	31	32
75°	8	11
85°	0	1
90°	0	



TEST NUMBER: P236150

CATALOG NUMBER: FLD6BX40D010 EU6B3/58040 F6LBXVM1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	4034.8
2.5°	4019.2
5°	3964.5
7.5°	3855.0
10°	3737.7
12.5°	3581.3
15°	3424.9
17.5°	3268.5
20°	3112.1
22.5°	2924.5
25°	2721.2
27.5°	2439.7
30°	2126.9
32.5°	1751.6
35°	1376.2
37.5°	1047.8
40°	766.3
42.5°	555.2
45°	383.2
47.5°	258.0
50°	172.0
52.5°	117.3
55°	93.8
57.5°	70.4
60°	54.7
62.5°	39.1
65°	31.3
67.5°	23.5
70°	15.6
72.5°	15.6
75°	7.8
77.5°	7.8
80°	7.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)