

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P364765

Luminaire Tested: **FLD6BX30D010-FEU6B35-8040-F6LBXVM1-LI-BL86**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P364765  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-43)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD6BX30D010-FEU6B35-8040-F6LBXVM1-LI-BL86  
Description: VANDAL RESISTANT ENCLOSED BOTTOM LENS, SPECULAR CLEAR REFLECTOR,  
BOTTOM LENS POLYCARBONATE, CLEAR 0.250", 3000LM  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2638.1 lumens  
Efficiency: N/A  
Efficacy: 97.7 lumens/watt  
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.82  
Luminous Opening: Circular (Dia: 0.71' x H: 0')  
CIE Type: Direct


Input Watts (W): 27  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P364765

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8040-F6LBXVM1-LI-BL86

### Luminous Intensity Polar Plot





TEST NUMBER: P364765

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8040-F6LBXVM1-LI-BL86

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	109	104	100	97	106	102	99	96	99	96	94		96	94	92		93	91	90	88
3	103	97	93	89	101	96	92	88	93	90	87		91	88	85		89	86	84	83
4	99	91	86	82	97	90	85	82	88	84	81		86	83	80		84	81	79	77
5	94	86	80	76	92	85	80	76	83	79	75		82	78	75		80	77	74	73
6	90	81	75	71	88	80	75	71	79	74	71		77	73	70		76	73	70	68
7	85	77	71	67	84	76	71	67	75	70	66		74	69	66		72	69	66	64
8	82	72	67	63	80	72	67	63	71	66	63		70	65	62		69	65	62	61
9	78	69	63	59	77	68	63	59	67	62	59		66	62	59		66	62	59	57
10	74	65	60	56	73	65	60	56	64	59	56		63	59	56		63	58	56	54

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	101495
5°	99566
10°	91947
15°	81935
20°	69973
25°	58765
30°	46132
35°	23906
40°	11418
45°	4493
50°	1181
55°	333
60°	219
65°	194
70°	160
75°	211
80°	157
85°	313



TEST NUMBER: P364765

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8040-F6LBXVM1-LI-BL86

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	336.7	12.8
10°-20°	805.3	30.5
20°-30°	889.1	33.7
30°-40°	489.2	18.5
40°-50°	103.4	3.9
50°-60°	8.8	0.3
60°-70°	2.7	0.1
70°-80°	2.0	0.1
80°-90°	1.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2031.0	77.0
0°-40°	2520.2	95.5
0°-60°	2632.4	99.8
0°-90°	2638.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2638.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3716	
5°	3631	337
15°	2897	805
25°	1950	889
35°	717	489
45°	116	103
55°	7	9
65°	3	3
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P364765

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8040-F6LBXVM1-LI-BL86

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3715.7
2.5°	3713.7
5°	3631.2
7.5°	3503.9
10°	3315.0
12.5°	3127.1
15°	2897.4
17.5°	2663.7
20°	2407.2
22.5°	2182.5
25°	1949.8
27.5°	1725.1
30°	1462.6
32.5°	1116.6
35°	716.9
37.5°	483.2
40°	320.2
42.5°	199.9
45°	116.3
47.5°	59.7
50°	27.8
52.5°	11.9
55°	7.0
57.5°	5.0
60°	4.0
62.5°	3.0
65°	3.0
67.5°	2.0
70°	2.0
72.5°	3.0
75°	2.0
77.5°	1.0
80°	1.0
82.5°	1.0
85°	1.0
87.5°	1.0
90°	0.0

(END OF REPORT)