

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P364778

Luminaire Tested: **FLD6BX30D010-FEU6B35-8040-F6LBXVM1-LI-BTR89BV**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P364778
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-22)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX30D010-FEU6B35-8040-F6LBXVM1-LI-BTR89BV
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, SPECULAR CLEAR REFLECTOR, BOTTOM TRIM ACRYLIC, CLEAR 0.125", 3000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2396.0 lumens
Efficiency: N/A
Efficacy: 88.7 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.77
Luminous Opening: Circular (Dia: 0.44' x H: 0')
CIE Type: Direct


Input Watts (W): 27
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P364778

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8040-F6LBXVM1-LI-BTR89BV

Luminous Intensity Polar Plot





TEST NUMBER: P364778

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8040-F6LBXVM1-LI-BTR89BV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	109	104	100	97	107	102	99	96	99	96	94		96	94	92		94	92	90	89
3	104	98	93	90	102	97	92	89	94	90	87		92	89	86		89	87	85	83
4	99	92	87	83	97	91	86	83	89	85	82		87	84	81		85	82	80	79
5	95	87	82	78	93	86	81	77	84	80	77		83	79	76		81	78	75	74
6	91	82	77	73	89	82	76	73	80	76	72		79	75	72		78	74	71	70
7	87	78	73	69	85	77	72	69	76	72	68		75	71	68		74	70	68	66
8	83	74	69	65	82	74	68	65	73	68	65		72	67	64		71	67	64	63
9	79	71	65	62	78	70	65	61	69	65	61		68	64	61		68	64	61	60
10	76	67	62	58	75	67	62	58	66	61	58		65	61	58		65	61	58	57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	268478
5°	262237
10°	241029
15°	214511
20°	181692
25°	144482
30°	101579
35°	42394
40°	14637
45°	3787
50°	1916
55°	1760
60°	1733
65°	1711
70°	1696
75°	2241
80°	2515
85°	4190



TEST NUMBER: P364778

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8040-F6LBXVM1-LI-BTR89BV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	337.8	14.1
10°-20°	801.6	33.5
20°-30°	827.1	34.5
30°-40°	351.8	14.7
40°-50°	42.2	1.8
50°-60°	12.8	0.5
60°-70°	10.0	0.4
70°-80°	8.0	0.3
80°-90°	4.7	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1966.5	82.1
0°-40°	2318.3	96.8
0°-60°	2373.3	99.1
0°-90°	2396.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2396.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3750	
5°	3648	338
15°	2894	802
25°	1829	827
35°	485	352
45°	37	42
55°	14	13
65°	10	10
75°	8	8
85°	5	5
90°	0	



TEST NUMBER: P364778

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8040-F6LBXVM1-LI-BTR89BV

CANDELA DISTRIBUTION (FULL):

	0°
0°	3749.6
2.5°	3725.3
5°	3648.5
7.5°	3515.1
10°	3315.1
12.5°	3118.1
15°	2893.8
17.5°	2641.2
20°	2384.5
22.5°	2116.8
25°	1828.8
27.5°	1531.7
30°	1228.6
32.5°	871.0
35°	485.0
37.5°	278.9
40°	156.6
42.5°	80.8
45°	37.4
47.5°	20.2
50°	17.2
52.5°	15.2
55°	14.1
57.5°	13.1
60°	12.1
62.5°	11.1
65°	10.1
67.5°	9.1
70°	8.1
72.5°	8.1
75°	8.1
77.5°	7.1
80°	6.1
82.5°	6.1
85°	5.1
87.5°	3.0
90°	0.0

(END OF REPORT)