

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P364801

Luminaire Tested: **FLD6BX40D010-FEU6B35-8027-F6LBXVM1-LI-BL86**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P364801  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-43)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD6BX40D010-FEU6B35-8027-F6LBXVM1-LI-BL86  
Description: VANDAL RESISTANT ENCLOSED BOTTOM LENS, SPECULAR CLEAR REFLECTOR,  
BOTTOM LENS POLYCARBONATE, CLEAR 0.250", 4000LM  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3438.0 lumens  
Efficiency: N/A  
Efficacy: 84.7 lumens/watt  
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.82  
Luminous Opening: Circular (Dia: 0.71' x H: 0')  
CIE Type: Direct


Input Watts (W): 40.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P364801

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8027-F6LBXVM1-LI-BL86

### Luminous Intensity Polar Plot





TEST NUMBER: P364801

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8027-F6LBXVM1-LI-BL86

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	109	104	100	97	106	102	99	96	99	96	94		96	94	92		93	91	90	88
3	103	97	93	89	101	96	92	88	93	90	87		91	88	85		89	86	84	83
4	99	91	86	82	97	90	85	82	88	84	81		86	83	80		84	81	79	77
5	94	86	80	76	92	85	80	76	83	79	75		82	78	75		80	77	74	73
6	90	81	75	71	88	80	75	71	79	74	71		77	73	70		76	73	70	68
7	85	77	71	67	84	76	71	67	75	70	66		74	69	66		72	69	66	64
8	82	72	67	63	80	72	67	63	71	66	63		70	65	62		69	65	62	61
9	78	69	63	59	77	68	63	59	67	62	59		66	62	59		66	62	59	57
10	74	65	60	56	74	65	60	56	64	59	56		63	59	56		63	58	56	54

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	132274
5°	129758
10°	119831
15°	106781
20°	91193
25°	76586
30°	60123
35°	31155
40°	14880
45°	5856
50°	1543
55°	433
60°	284
65°	252
70°	208
75°	274
80°	204
85°	407



TEST NUMBER: P364801

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8027-F6LBXVM1-LI-BL86

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	438.8	12.8
10°-20°	1049.4	30.5
20°-30°	1158.7	33.7
30°-40°	637.6	18.5
40°-50°	134.8	3.9
50°-60°	11.4	0.3
60°-70°	3.5	0.1
70°-80°	2.6	0.1
80°-90°	1.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2647.0	77.0
0°-40°	3284.5	95.5
0°-60°	3430.7	99.8
0°-90°	3438.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3438.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4842	
5°	4732	439
15°	3776	1049
25°	2541	1159
35°	934	638
45°	152	135
55°	9	11
65°	4	4
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P364801

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8027-F6LBXVM1-LI-BL86

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	4842.5
2.5°	4839.9
5°	4732.3
7.5°	4566.5
10°	4320.3
12.5°	4075.4
15°	3776.0
17.5°	3471.5
20°	3137.2
22.5°	2844.3
25°	2541.1
27.5°	2248.3
30°	1906.2
32.5°	1455.2
35°	934.3
37.5°	629.8
40°	417.3
42.5°	260.5
45°	151.6
47.5°	77.7
50°	36.3
52.5°	15.5
55°	9.1
57.5°	6.5
60°	5.2
62.5°	3.9
65°	3.9
67.5°	2.6
70°	2.6
72.5°	3.9
75°	2.6
77.5°	1.3
80°	1.3
82.5°	1.3
85°	1.3
87.5°	1.3
90°	0.0

(END OF REPORT)