

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P364808

Luminaire Tested: **FLD6BX40D010-FEU6B35-8027-F6LBXVM1-LI-BTR82**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P364808
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-26)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX40D010-FEU6B35-8027-F6LBXVM1-LI-BTR82
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, SPECULAR CLEAR REFLECTOR, BOTTOM TRIM POLYCARBONATE, PATTERN 12 0.187", 4000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2877.0 lumens
Efficiency: N/A
Efficacy: 70.9 lumens/watt
Spacing Criteria (0/90/45): 1.07 / 1.07 / 1.07
Luminous Opening: Circular (Dia: 0.44' x H: 0')
CIE Type: Direct


Input Watts (W): 40.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P364808

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8027-F6LBXVM1-LI-BTR82

Luminous Intensity Polar Plot





TEST NUMBER: P364808

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8027-F6LBXVM1-LI-BTR82

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	103	110	107	104	101	102	100	98		99	97	95		95	94	93	91
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88	85	83	81
3	98	90	84	79	96	89	83	79	86	81	77		84	80	76		81	78	75	73
4	92	83	76	71	90	81	75	70	79	74	69		77	72	69		75	71	68	66
5	86	76	69	64	84	75	68	63	73	67	63		71	66	62		69	65	61	60
6	81	70	63	57	79	69	62	57	67	61	57		66	60	56		64	60	56	54
7	76	65	57	52	74	64	57	52	62	56	52		61	56	52		60	55	51	50
8	71	60	53	48	70	59	53	48	58	52	48		57	51	47		56	51	47	46
9	67	56	49	44	66	55	49	44	54	48	44		53	48	44		52	47	43	42
10	63	52	45	41	62	52	45	41	51	45	41		50	44	40		49	44	40	39

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	139387
5°	139539
10°	141058
15°	139812
20°	133985
25°	123412
30°	109227
35°	93144
40°	76084
45°	59480
50°	43866
55°	30422
60°	19433
65°	11826
70°	7997
75°	6197
80°	5443
85°	7558



TEST NUMBER: P364808

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8027-F6LBXVM1-LI-BTR82

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	185.4	6.4
10°-20°	527.4	18.3
20°-30°	713.4	24.8
30°-40°	663.6	23.1
40°-50°	454.7	15.8
50°-60°	224.1	7.8
60°-70°	74.9	2.6
70°-80°	24.8	0.9
80°-90°	8.6	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1426.3	49.6
0°-40°	2089.9	72.6
0°-60°	2768.7	96.2
0°-90°	2877.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2877.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1947	
5°	1941	185
15°	1886	527
25°	1562	713
35°	1066	664
45°	587	455
55°	244	224
65°	70	75
75°	22	25
85°	9	9
90°	0	



TEST NUMBER: P364808

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8027-F6LBXVM1-LI-BTR82

CANDELA DISTRIBUTION (FULL):

	0°
0°	1946.7
2.5°	1944.1
5°	1941.4
7.5°	1944.1
10°	1940.1
12.5°	1919.0
15°	1886.1
17.5°	1825.5
20°	1758.4
22.5°	1668.8
25°	1562.1
27.5°	1446.2
30°	1321.1
32.5°	1195.9
35°	1065.6
37.5°	936.5
40°	814.0
42.5°	695.4
45°	587.4
47.5°	484.7
50°	393.8
52.5°	314.8
55°	243.7
57.5°	185.7
60°	135.7
62.5°	97.5
65°	69.8
67.5°	50.1
70°	38.2
72.5°	29.0
75°	22.4
77.5°	17.1
80°	13.2
82.5°	10.5
85°	9.2
87.5°	5.3
90°	0.0

(END OF REPORT)