

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P366204

Luminaire Tested: **FLD6BX30D010-FEU6B35-8040-F6LBXVM1-WMH-BL85**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P366204
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-47)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX30D010-FEU6B35-8040-F6LBXVM1-WMH-BL85
Description: VANDAL RESISTANT ENCLOSED BOTTOM LENS, WARM HAZE REFLECTOR, BOTTOM LENS POLYCARBONATE, CLEAR 0.187", 3000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2640.0 lumens
Efficiency: N/A
Efficacy: 97.8 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.85
Luminous Opening: Circular (Dia: 0.71' x H: 0')
CIE Type: Direct


Input Watts (W): 27
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P366204

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8040-F6LBXVM1-WMH-BL85

Luminous Intensity Polar Plot





TEST NUMBER: P366204

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8040-F6LBXVM1-WMH-BL85

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	102	101	100	99	98	97	96	94
2	108	104	100	97	106	102	98	95	99	96	93	96	93	91	93	91	89	88
3	103	97	92	88	101	96	91	88	93	89	86	91	88	85	88	86	84	82
4	98	91	86	82	96	90	85	81	88	83	80	86	82	79	84	81	78	77
5	93	85	80	76	92	85	79	75	83	78	75	81	77	74	80	76	73	72
6	89	80	75	71	88	80	74	70	78	73	70	77	73	69	76	72	69	68
7	85	76	70	66	83	75	70	66	74	69	65	73	68	65	72	68	65	63
8	81	72	66	62	80	71	66	62	70	65	62	69	65	61	68	64	61	60
9	77	68	62	58	76	67	62	58	66	62	58	66	61	58	65	61	58	56
10	74	64	59	55	73	64	59	55	63	58	55	62	58	55	62	58	55	53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	92875
5°	92484
10°	87853
15°	79803
20°	69441
25°	59039
30°	46441
35°	26497
40°	11924
45°	5018
50°	1585
55°	481
60°	328
65°	259
70°	240
75°	317
80°	157
85°	313



TEST NUMBER: P366204

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8040-F6LBXVM1-WMH-BL85

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	315.5	12.0
10°-20°	785.0	29.7
20°-30°	889.5	33.7
30°-40°	515.7	19.5
40°-50°	114.3	4.3
50°-60°	12.5	0.5
60°-70°	4.1	0.2
70°-80°	2.6	0.1
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1990.0	75.4
0°-40°	2505.7	94.9
0°-60°	2632.6	99.7
0°-90°	2640.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2640.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3400	
5°	3373	315
15°	2822	785
25°	1959	890
35°	795	516
45°	130	114
55°	10	13
65°	4	4
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P366204

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8040-F6LBXVM1-WMH-BL85

CANDELA DISTRIBUTION (FULL):

0°	
0°	3400.1
2.5°	3403.1
5°	3372.9
7.5°	3299.3
10°	3167.4
12.5°	3007.3
15°	2822.0
17.5°	2626.6
20°	2388.9
22.5°	2174.4
25°	1958.9
27.5°	1729.2
30°	1472.4
32.5°	1169.3
35°	794.6
37.5°	510.6
40°	334.4
42.5°	218.5
45°	129.9
47.5°	72.5
50°	37.3
52.5°	17.1
55°	10.1
57.5°	8.1
60°	6.0
62.5°	5.0
65°	4.0
67.5°	3.0
70°	3.0
72.5°	3.0
75°	3.0
77.5°	2.0
80°	1.0
82.5°	1.0
85°	1.0
87.5°	0.0
90°	0.0

(END OF REPORT)