

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P366239

Luminaire Tested: **FLD6BX40D010-FEU6B35-8027-F6LBXVM1-WMH-BL84**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P366239  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-47)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD6BX40D010-FEU6B35-8027-F6LBXVM1-WMH-BL84  
Description: VANDAL RESISTANT ENCLOSED BOTTOM LENS, WARM HAZE REFLECTOR, BOTTOM LENS POLYCARBONATE, CLEAR 0.125", 4000LM  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3452.1 lumens  
Efficiency: N/A  
Efficacy: 85.0 lumens/watt  
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.85  
Luminous Opening: Circular (Dia: 0.71' x H: 0')  
CIE Type: Direct


Input Watts (W): 40.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P366239

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8027-F6LBXVM1-WMH-BL84

### Luminous Intensity Polar Plot





TEST NUMBER: P366239

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8027-F6LBXVM1-WMH-BL84

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	108	104	100	97	106	102	98	95	99	96	93		96	93	91		93	91	89	88
3	103	97	92	88	101	96	91	88	93	89	86		91	88	85		88	86	84	82
4	98	91	86	82	96	90	85	81	88	83	80		86	82	79		84	81	78	77
5	93	85	80	76	92	85	79	75	83	78	75		81	77	74		80	76	73	72
6	89	80	75	71	88	80	74	70	78	73	70		77	73	69		76	72	69	68
7	85	76	70	66	83	75	70	66	74	69	65		73	68	65		72	68	65	63
8	81	72	66	62	80	71	66	62	70	65	62		69	65	61		68	64	61	60
9	77	68	62	58	76	67	62	58	66	62	58		66	61	58		65	61	58	56
10	74	64	59	55	73	64	59	55	63	58	55		62	58	55		62	58	55	53

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	121438
5°	120929
10°	114874
15°	104346
20°	90801
25°	77198
30°	60726
35°	34646
40°	15589
45°	6563
50°	2070
55°	629
60°	432
65°	343
70°	319
75°	422
80°	204
85°	407



TEST NUMBER: P366239

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8027-F6LBXVM1-WMH-BL84

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	412.5	12.0
10°-20°	1026.4	29.7
20°-30°	1163.1	33.7
30°-40°	674.3	19.5
40°-50°	149.5	4.3
50°-60°	16.4	0.5
60°-70°	5.4	0.2
70°-80°	3.5	0.1
80°-90°	0.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2602.1	75.4
0°-40°	3276.4	94.9
0°-60°	3442.3	99.7
0°-90°	3452.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3452.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4446	
5°	4410	413
15°	3690	1026
25°	2561	1163
35°	1039	674
45°	170	150
55°	13	16
65°	5	5
75°	4	3
85°	1	1
90°	0	



TEST NUMBER: P366239

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8027-F6LBXVM1-WMH-BL84

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	4445.8
2.5°	4449.8
5°	4410.3
7.5°	4314.1
10°	4141.6
12.5°	3932.2
15°	3689.9
17.5°	3434.5
20°	3123.7
22.5°	2843.2
25°	2561.4
27.5°	2261.1
30°	1925.3
32.5°	1528.9
35°	1039.0
37.5°	667.7
40°	437.2
42.5°	285.8
45°	169.9
47.5°	94.8
50°	48.7
52.5°	22.4
55°	13.2
57.5°	10.5
60°	7.9
62.5°	6.6
65°	5.3
67.5°	4.0
70°	4.0
72.5°	4.0
75°	4.0
77.5°	2.6
80°	1.3
82.5°	1.3
85°	1.3
87.5°	0.0
90°	0.0

(END OF REPORT)