

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P366220

Luminaire Tested: **FLD6BX30D010-FEU6B35-8040-F6LBXVM1-WMH**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P366220  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-11)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD6BX30D010-FEU6B35-8040-F6LBXVM1-WMH  
Description: VANDAL RESISTANT OPEN, WARM HAZE REFLECTOR, 3000LM  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2890.0 lumens  
Efficiency: N/A  
Efficacy: 107.0 lumens/watt  
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.84  
Luminous Opening: Circular (Dia: 0.71' x H: 0')  
CIE Type: Direct


Input Watts (W): 27  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P366220

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8040-F6LBXVM1-WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P366220

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8040-F6LBXVM1-WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94
2	109	104	100	97	106	102	99	96	99	96	94	96	94	92	93	91	90	88
3	103	97	93	89	101	96	92	88	93	90	87	91	88	85	89	86	84	82
4	98	91	86	82	97	90	85	82	88	84	81	86	83	80	84	81	79	77
5	94	86	80	76	92	85	80	76	83	79	75	82	78	75	80	77	74	72
6	89	81	75	71	88	80	75	71	79	74	70	77	73	70	76	72	69	68
7	85	76	71	67	84	76	70	66	74	70	66	73	69	66	72	68	65	64
8	81	72	66	63	80	72	66	62	71	66	62	70	65	62	69	65	62	60
9	78	68	63	59	77	68	62	59	67	62	59	66	62	58	65	61	58	57
10	74	65	59	56	73	64	59	56	64	59	55	63	58	55	62	58	55	54

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	104260
5°	103216
10°	98046
15°	89132
20°	77109
25°	65299
30°	50967
35°	28374
40°	12430
45°	4999
50°	1373
55°	243
60°	164
65°	129
70°	80
75°	106
80°	0
85°	0



TEST NUMBER: P366220

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8040-F6LBXVM1-WMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	351.9	12.2
10°-20°	874.6	30.3
20°-30°	982.4	34.0
30°-40°	555.9	19.2
40°-50°	114.6	4.0
50°-60°	8.3	0.3
60°-70°	1.7	0.1
70°-80°	0.7	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2208.9	76.4
0°-40°	2764.7	95.7
0°-60°	2887.6	99.9
0°-90°	2890.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2890.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3817	
5°	3764	352
15°	3152	875
25°	2167	982
35°	851	556
45°	129	115
55°	5	8
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P366220

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8040-F6LBXVM1-WMH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	3816.9
2.5°	3800.7
5°	3764.3
7.5°	3674.4
10°	3534.9
12.5°	3361.1
15°	3151.9
17.5°	2914.5
20°	2652.7
22.5°	2402.1
25°	2166.6
27.5°	1905.9
30°	1615.9
32.5°	1278.4
35°	850.9
37.5°	533.6
40°	348.6
42.5°	220.3
45°	129.4
47.5°	68.7
50°	32.3
52.5°	11.1
55°	5.1
57.5°	4.0
60°	3.0
62.5°	2.0
65°	2.0
67.5°	1.0
70°	1.0
72.5°	1.0
75°	1.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)