

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P364821

Luminaire Tested: **FLD6BX40D010-FEU6B35-8030-F6LBXVM1-LI-BL89AM**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P364821
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-44)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX40D010-FEU6B35-8030-F6LBXVM1-LI-BL89AM
Description: VANDAL RESISTANT ENCLOSED BOTTOM LENS, SPECULAR CLEAR REFLECTOR,
BOTTOM LENS POLYCARBONATE, OPAL SMOOTH 0.125", 4000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1581.0 lumens
Efficiency: N/A
Efficacy: 38.9 lumens/watt
Spacing Criteria (0/90/45): 1.25 / 1.25 / 1.37
Luminous Opening: Circular (Dia: 0.71' x H: 0')
CIE Type: Direct


Input Watts (W): 40.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P364821

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8030-F6LBXVM1-LI-BL89AM

Luminous Intensity Polar Plot





TEST NUMBER: P364821

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8030-F6LBXVM1-LI-BL89AM

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	109	104	100	96	106	102	98	94	98	94	91		94	91	89		90	88	86	84
2	99	91	84	78	96	89	83	77	85	80	75		82	78	74		79	75	72	70
3	90	80	71	65	88	78	70	64	75	68	63		72	67	62		70	65	61	59
4	82	70	62	55	80	69	61	54	67	59	54		64	58	53		62	57	52	50
5	76	63	54	47	74	62	53	47	60	52	46		58	51	46		56	50	45	43
6	70	57	48	41	68	56	47	41	54	46	41		52	45	40		51	45	40	38
7	65	51	42	36	63	50	42	36	49	41	36		47	41	36		46	40	35	33
8	60	47	38	32	59	46	38	32	45	37	32		43	37	32		42	36	32	30
9	56	43	35	29	55	42	34	29	41	34	29		40	33	29		39	33	29	27
10	53	40	32	26	52	39	31	26	38	31	26		37	31	26		36	30	26	24

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	15269
5°	15215
10°	15161
15°	15107
20°	15008
25°	14898
30°	14808
35°	14645
40°	14534
45°	14362
50°	14159
55°	13834
60°	13466
65°	12901
70°	11988
75°	10607
80°	8667
85°	5610



TEST NUMBER: P364821

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8030-F6LBXVM1-LI-BL89AM

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.7	3.3
10°-20°	150.7	9.5
20°-30°	228.2	14.4
30°-40°	275.0	17.4
40°-50°	286.6	18.1
50°-60°	260.1	16.4
60°-70°	196.9	12.5
70°-80°	107.2	6.8
80°-90°	23.6	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	431.6	27.3
0°-40°	706.6	44.7
0°-60°	1253.3	79.3
0°-90°	1581.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1581.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	559	
5°	555	53
15°	534	151
25°	494	228
35°	439	275
45°	372	287
55°	290	260
65°	200	197
75°	100	107
85°	18	24
90°	0	



TEST NUMBER: P364821

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8030-F6LBXVM1-LI-BL89AM

CANDELA DISTRIBUTION (FULL):

0°	
0°	559.0
2.5°	557.6
5°	554.9
7.5°	552.1
10°	546.6
12.5°	541.1
15°	534.2
17.5°	526.0
20°	516.3
22.5°	506.7
25°	494.3
27.5°	483.3
30°	469.5
32.5°	455.7
35°	439.2
37.5°	422.7
40°	407.6
42.5°	389.7
45°	371.8
47.5°	352.5
50°	333.2
52.5°	312.6
55°	290.5
57.5°	269.9
60°	246.5
62.5°	223.1
65°	199.6
67.5°	174.9
70°	150.1
72.5°	126.7
75°	100.5
77.5°	77.1
80°	55.1
82.5°	34.4
85°	17.9
87.5°	6.9
90°	0.0

(END OF REPORT)