

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P364829

Luminaire Tested: **FLD6BX40D010-FEU6B35-8030-F6LBXVM1-LI-BTR86**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P364829
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-24)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX40D010-FEU6B35-8030-F6LBXVM1-LI-BTR86
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, SPECULAR CLEAR REFLECTOR, BOTTOM TRIM POLYCARBONATE, CLEAR 0.250", 4000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2995.0 lumens
Efficiency: N/A
Efficacy: 73.8 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.77
Luminous Opening: Circular (Dia: 0.44' x H: 0')
CIE Type: Direct


Input Watts (W): 40.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P364829

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8030-F6LBXVM1-LI-BTR86

Luminous Intensity Polar Plot





TEST NUMBER: P364829

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8030-F6LBXVM1-LI-BTR86

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94
2	109	104	100	97	107	102	99	96	99	96	94	96	94	92	94	92	90	89
3	104	98	93	90	102	97	92	89	94	90	87	92	89	86	89	87	85	83
4	99	92	87	83	97	91	86	83	89	85	82	87	84	81	85	82	80	78
5	95	87	82	78	93	86	81	77	84	80	77	83	79	76	81	78	75	74
6	91	82	77	73	89	82	76	73	80	76	72	79	75	72	78	74	71	70
7	87	78	73	69	85	77	72	69	76	72	68	75	71	68	74	70	68	66
8	83	74	69	65	82	74	68	65	73	68	65	72	67	64	71	67	64	63
9	79	71	65	62	78	70	65	61	69	65	61	68	64	61	68	64	61	60
10	76	67	62	58	75	67	62	58	66	61	58	65	61	58	65	61	58	57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	336149
5°	328492
10°	302830
15°	268224
20°	227083
25°	179908
30°	126432
35°	52656
40°	18068
45°	4830
50°	2651
55°	2484
60°	2277
65°	2236
70°	2219
75°	2573
80°	3257
85°	5422



TEST NUMBER: P364829

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8030-F6LBXVM1-LI-BTR86

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	423.5	14.1
10°-20°	1003.8	33.5
20°-30°	1030.5	34.4
30°-40°	436.4	14.6
40°-50°	53.7	1.8
50°-60°	17.8	0.6
60°-70°	13.1	0.4
70°-80°	10.2	0.3
80°-90°	6.1	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2457.9	82.1
0°-40°	2894.2	96.6
0°-60°	2965.6	99.0
0°-90°	2995.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2995.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4695	
5°	4570	424
15°	3618	1004
25°	2277	1031
35°	602	436
45°	48	54
55°	20	18
65°	13	13
75°	9	10
85°	7	6
90°	0	



TEST NUMBER: P364829

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8030-F6LBXVM1-LI-BTR86

CANDELA DISTRIBUTION (FULL):

	0°
0°	4694.7
2.5°	4664.3
5°	4570.3
7.5°	4408.8
10°	4165.1
12.5°	3905.7
15°	3618.4
17.5°	3309.9
20°	2980.2
22.5°	2629.4
25°	2277.2
27.5°	1913.1
30°	1529.2
32.5°	1077.7
35°	602.4
37.5°	345.6
40°	193.3
42.5°	101.9
45°	47.7
47.5°	27.8
50°	23.8
52.5°	21.2
55°	19.9
57.5°	18.5
60°	15.9
62.5°	14.6
65°	13.2
67.5°	11.9
70°	10.6
72.5°	10.6
75°	9.3
77.5°	9.3
80°	7.9
82.5°	7.9
85°	6.6
87.5°	4.0
90°	0.0

(END OF REPORT)