

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P365548

Luminaire Tested: **FLD6BX40D010-FEU6B35-8030-F6LBXVM1-MW-BTR85**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P365548
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-16)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX40D010-FEU6B35-8030-F6LBXVM1-MW-BTR85
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, MATTE WHITE REFLECTOR,
BOTTOM TRIM POLYCARBONATE, CLEAR 0.187", 4000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2429.0 lumens
Efficiency: N/A
Efficacy: 59.8 lumens/watt
Spacing Criteria (0/90/45): 0.87 / 0.87 / 0.84
Luminous Opening: Circular (Dia: 0.44' x H: 0')
CIE Type: Direct


Input Watts (W): 40.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P365548

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8030-F6LBXVM1-MW-BTR85

Luminous Intensity Polar Plot





TEST NUMBER: P365548

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8030-F6LBXVM1-MW-BTR85

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	103	110	107	104	101	102	100	98		99	97	95		95	94	92	91
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88	86	83	82
3	99	91	85	80	96	89	84	79	87	82	78		84	80	77		82	78	76	74
4	93	84	77	72	91	82	76	72	80	75	71		78	73	70		76	72	69	67
5	87	77	70	65	85	76	70	65	74	69	64		73	68	64		71	67	63	62
6	82	72	65	60	80	71	64	60	69	63	59		68	63	59		66	62	58	57
7	77	67	60	55	76	66	60	55	65	59	55		64	58	54		62	58	54	52
8	73	63	56	51	72	62	55	51	61	55	51		60	54	51		59	54	50	49
9	70	59	52	48	68	58	52	48	57	51	47		56	51	47		55	51	47	45
10	66	55	49	45	65	55	49	44	54	48	44		53	48	44		52	48	44	43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	168780
5°	165666
10°	157366
15°	147381
20°	134183
25°	111933
30°	81166
35°	55846
40°	41052
45°	33325
50°	28984
55°	25616
60°	22282
65°	18891
70°	15283
75°	11038
80°	7381
85°	7887



TEST NUMBER: P365548

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8030-F6LBXVM1-MW-BTR85

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	215.5	8.9
10°-20°	555.3	22.9
20°-30°	637.3	26.2
30°-40°	412.4	17.0
40°-50°	259.1	10.7
50°-60°	184.4	7.6
60°-70°	111.2	4.6
70°-80°	44.2	1.8
80°-90°	9.5	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
<hr/>		
0°-30°	1408.1	58.0
0°-40°	1820.5	74.9
0°-60°	2264.1	93.2
0°-90°	2429.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2429.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2357	
5°	2305	216
15°	1988	555
25°	1417	637
35°	639	412
45°	329	259
55°	205	184
65°	112	111
75°	40	44
85°	10	10
90°	0	



TEST NUMBER: P365548

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8030-F6LBXVM1-MW-BTR85

CANDELA DISTRIBUTION (FULL):

	0°
0°	2357.2
2.5°	2346.2
5°	2304.9
7.5°	2242.9
10°	2164.4
12.5°	2077.7
15°	1988.2
17.5°	1887.7
20°	1761.0
22.5°	1608.2
25°	1416.8
27.5°	1203.4
30°	981.7
32.5°	794.4
35°	638.9
37.5°	524.6
40°	439.2
42.5°	377.3
45°	329.1
47.5°	291.9
50°	260.2
52.5°	232.7
55°	205.2
57.5°	180.4
60°	155.6
62.5°	133.6
65°	111.5
67.5°	90.9
70°	73.0
72.5°	55.1
75°	39.9
77.5°	27.5
80°	17.9
82.5°	11.0
85°	9.6
87.5°	5.5
90°	0.0

(END OF REPORT)