

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P366233

Luminaire Tested: **FLD6BX30D010-FEU6B35-8050-F6LBXVM1-WMH-BTR86**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P366233
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-30)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX30D010-FEU6B35-8050-F6LBXVM1-WMH-BTR86
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, WARM HAZE REFLECTOR,
BOTTOM TRIM POLYCARBONATE, CLEAR 0.250", 3000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2217.1 lumens
Efficiency: N/A
Efficacy: 82.1 lumens/watt
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.8
Luminous Opening: Circular (Dia: 0.44' x H: 0')
CIE Type: Direct


Input Watts (W): 27
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P366233

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8050-F6LBXVM1-WMH-BTR86

Luminous Intensity Polar Plot





TEST NUMBER: P366233

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8050-F6LBXVM1-WMH-BTR86

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	109	104	100	97	106	102	99	96	99	96	94		96	94	92		93	92	90	88
3	104	98	93	89	102	96	92	89	94	90	87		91	88	86		89	87	84	83
4	99	92	87	83	97	91	86	82	89	85	81		87	83	80		85	82	80	78
5	94	87	81	77	93	86	81	77	84	80	76		82	79	76		81	78	75	74
6	90	82	76	72	89	81	76	72	80	75	72		78	74	71		77	74	71	69
7	86	78	72	68	85	77	72	68	76	71	68		75	70	67		73	70	67	66
8	82	74	68	64	81	73	68	64	72	67	64		71	67	64		70	66	63	62
9	79	70	64	61	78	69	64	61	69	64	60		68	63	60		67	63	60	59
10	76	67	61	58	75	66	61	58	65	61	57		65	60	57		64	60	57	56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	229212
5°	225444
10°	214804
15°	196290
20°	168327
25°	135065
30°	94700
35°	43749
40°	14048
45°	4536
50°	2105
55°	1860
60°	1847
65°	1694
70°	1675
75°	1937
80°	2474
85°	4108



TEST NUMBER: P366233

CATALOG NUMBER: FLD6BX30D010-FEUGB35-8050-F6LBXVM1-WMH-BTR86

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	294.2	13.3
10°-20°	732.8	33.1
20°-30°	769.5	34.7
30°-40°	341.5	15.4
40°-50°	44.1	2.0
50°-60°	13.8	0.6
60°-70°	9.7	0.4
70°-80°	7.1	0.3
80°-90°	4.4	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1796.5	81.0
0°-40°	2137.9	96.4
0°-60°	2195.8	99.0
0°-90°	2217.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2217.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3201	
5°	3137	294
15°	2648	733
25°	1710	770
35°	500	341
45°	45	44
55°	15	14
65°	10	10
75°	7	7
85°	5	4
90°	0	



TEST NUMBER: P366233

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8050-F6LBXVM1-WMH-BTR86

CANDELA DISTRIBUTION (FULL):

	0°
0°	3201.2
2.5°	3181.3
5°	3136.6
7.5°	3075.8
10°	2954.4
12.5°	2818.1
15°	2648.0
17.5°	2444.0
20°	2209.1
22.5°	1962.3
25°	1709.6
27.5°	1426.0
30°	1145.4
32.5°	841.9
35°	500.5
37.5°	266.7
40°	150.3
42.5°	82.6
45°	44.8
47.5°	22.9
50°	18.9
52.5°	16.9
55°	14.9
57.5°	13.9
60°	12.9
62.5°	10.9
65°	10.0
67.5°	8.0
70°	8.0
72.5°	7.0
75°	7.0
77.5°	6.0
80°	6.0
82.5°	5.0
85°	5.0
87.5°	3.0
90°	0.0

(END OF REPORT)