

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P365552

Luminaire Tested: **FLD6BX40D010-FEU6B35-8030-F6LBXVM1-MW-BTR89BV**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P365552
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-12)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX40D010-FEU6B35-8030-F6LBXVM1-MW-BTR89BV
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, MATTE WHITE REFLECTOR,
BOTTOM TRIM ACRYLIC, CLEAR 0.125", 4000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2580.0 lumens
Efficiency: N/A
Efficacy: 63.5 lumens/watt
Spacing Criteria (0/90/45): 0.87 / 0.87 / 0.84
Luminous Opening: Circular (Dia: 0.44' x H: 0')
CIE Type: Direct


Input Watts (W): 40.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P365552

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8030-F6LBXVM1-MW-BTR89BV

Luminous Intensity Polar Plot





TEST NUMBER: P365552

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8030-F6LBXVM1-MW-BTR89BV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|----|-----|
| RF | 20 | | | | | 20 | | | | | 20 | | | | | 20 | | | | | 20 | |
| RC | 80 | | | | | 70 | | | | | 50 | | | | | 30 | | | | | 10 | 0 |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 | |
| RCR | | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | | 100 |
| 1 | 112 | 109 | 106 | 103 | 110 | 107 | 104 | 101 | 102 | 100 | 98 | 99 | 97 | 95 | 95 | 94 | 92 | 91 | | | | 91 |
| 2 | 105 | 99 | 94 | 90 | 103 | 97 | 93 | 89 | 94 | 90 | 87 | 91 | 88 | 85 | 88 | 86 | 83 | 82 | | | | 82 |
| 3 | 99 | 91 | 85 | 80 | 96 | 89 | 84 | 79 | 87 | 82 | 78 | 84 | 80 | 77 | 82 | 78 | 76 | 74 | | | | 74 |
| 4 | 93 | 84 | 77 | 72 | 91 | 82 | 76 | 72 | 80 | 75 | 71 | 78 | 74 | 70 | 76 | 72 | 69 | 67 | | | | 67 |
| 5 | 87 | 77 | 70 | 65 | 85 | 76 | 70 | 65 | 74 | 69 | 64 | 73 | 68 | 64 | 71 | 67 | 63 | 62 | | | | 62 |
| 6 | 82 | 72 | 65 | 60 | 80 | 71 | 64 | 60 | 69 | 64 | 59 | 68 | 63 | 59 | 66 | 62 | 58 | 57 | | | | 57 |
| 7 | 78 | 67 | 60 | 55 | 76 | 66 | 60 | 55 | 65 | 59 | 55 | 64 | 58 | 54 | 62 | 58 | 54 | 53 | | | | 53 |
| 8 | 73 | 63 | 56 | 51 | 72 | 62 | 56 | 51 | 61 | 55 | 51 | 60 | 54 | 51 | 59 | 54 | 50 | 49 | | | | 49 |
| 9 | 70 | 59 | 52 | 48 | 68 | 58 | 52 | 48 | 57 | 51 | 47 | 56 | 51 | 47 | 55 | 51 | 47 | 46 | | | | 46 |
| 10 | 66 | 55 | 49 | 45 | 65 | 55 | 49 | 45 | 54 | 48 | 44 | 53 | 48 | 44 | 52 | 48 | 44 | 43 | | | | 43 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|--------|
| | 0° |
| 0° | 180251 |
| 5° | 176684 |
| 10° | 168221 |
| 15° | 157121 |
| 20° | 143151 |
| 25° | 119501 |
| 30° | 85920 |
| 35° | 59307 |
| 40° | 43351 |
| 45° | 35117 |
| 50° | 30666 |
| 55° | 27151 |
| 60° | 23657 |
| 65° | 20060 |
| 70° | 16141 |
| 75° | 11426 |
| 80° | 7958 |
| 85° | 9037 |



TEST NUMBER: P365552

CATALOG NUMBER: FLD6BX40D010-FEUGB35-8030-F6LBXVM1-MW-BTR89BV

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 230.4 | 8.9 |
| 10°-20° | 592.8 | 23.0 |
| 20°-30° | 677.5 | 26.3 |
| 30°-40° | 435.9 | 16.9 |
| 40°-50° | 273.2 | 10.6 |
| 50°-60° | 195.1 | 7.6 |
| 60°-70° | 118.3 | 4.6 |
| 70°-80° | 46.4 | 1.8 |
| 80°-90° | 10.5 | 0.4 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 1500.7 | 58.2 |
| 0°-40° | 1936.6 | 75.1 |
| 0°-60° | 2404.8 | 93.2 |
| 0°-90° | 2580.0 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 2580.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 2517 | |
| 5° | 2458 | 230 |
| 15° | 2120 | 593 |
| 25° | 1513 | 678 |
| 35° | 678 | 436 |
| 45° | 347 | 273 |
| 55° | 218 | 195 |
| 65° | 118 | 118 |
| 75° | 41 | 46 |
| 85° | 11 | 10 |
| 90° | 0 | |



TEST NUMBER: P365552

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8030-F6LBXVM1-MW-BTR89BV

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|--------|
| 0° | 2517.4 |
| 2.5° | 2505.0 |
| 5° | 2458.2 |
| 7.5° | 2401.7 |
| 10° | 2313.7 |
| 12.5° | 2224.2 |
| 15° | 2119.6 |
| 17.5° | 2012.2 |
| 20° | 1878.7 |
| 22.5° | 1713.6 |
| 25° | 1512.6 |
| 27.5° | 1270.4 |
| 30° | 1039.2 |
| 32.5° | 835.4 |
| 35° | 678.5 |
| 37.5° | 554.7 |
| 40° | 463.8 |
| 42.5° | 396.4 |
| 45° | 346.8 |
| 47.5° | 308.3 |
| 50° | 275.3 |
| 52.5° | 246.4 |
| 55° | 217.5 |
| 57.5° | 189.9 |
| 60° | 165.2 |
| 62.5° | 141.8 |
| 65° | 118.4 |
| 67.5° | 97.7 |
| 70° | 77.1 |
| 72.5° | 57.8 |
| 75° | 41.3 |
| 77.5° | 28.9 |
| 80° | 19.3 |
| 82.5° | 12.4 |
| 85° | 11.0 |
| 87.5° | 5.5 |
| 90° | 0.0 |

(END OF REPORT)