

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P364836

Luminaire Tested: **FLD6BX40D010-FEU6B35-8035-F6LBXVM1-LI-BL85**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P364836
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-43)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX40D010-FEU6B35-8035-F6LBXVM1-LI-BL85
Description: VANDAL RESISTANT ENCLOSED BOTTOM LENS, SPECULAR CLEAR REFLECTOR,
BOTTOM LENS POLYCARBONATE, CLEAR 0.187", 4000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3713.0 lumens
Efficiency: N/A
Efficacy: 91.5 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.82
Luminous Opening: Circular (Dia: 0.71' x H: 0')
CIE Type: Direct


Input Watts (W): 40.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P364836

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8035-F6LBXVM1-LI-BL85

Luminous Intensity Polar Plot





TEST NUMBER: P364836

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8035-F6LBXVM1-LI-BL85

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	109	104	100	97	106	102	99	96	99	96	94		96	94	92		93	91	90	88
3	103	97	93	89	101	96	92	88	93	90	87		91	88	85		89	86	84	83
4	99	91	86	82	97	90	85	82	88	84	81		86	83	80		84	81	79	77
5	94	86	80	76	92	85	80	76	83	79	75		82	78	75		80	77	74	73
6	90	81	75	71	88	80	75	71	79	74	71		77	73	70		76	73	70	68
7	85	77	71	67	84	76	71	67	75	70	66		74	69	66		72	69	66	64
8	82	72	67	63	80	72	67	63	71	66	63		70	65	62		69	65	62	61
9	78	69	63	59	77	68	63	59	67	62	59		66	62	59		66	62	59	57
10	74	65	60	56	74	65	60	56	64	59	56		63	59	56		63	58	56	54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	142853
5°	140139
10°	129414
15°	115324
20°	98486
25°	82714
30°	64930
35°	33646
40°	16067
45°	6324
50°	1666
55°	467
60°	306
65°	271
70°	224
75°	296
80°	220
85°	439



TEST NUMBER: P364836

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8035-F6LBXVM1-LI-BL85

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	473.9	12.8
10°-20°	1133.4	30.5
20°-30°	1251.4	33.7
30°-40°	688.6	18.5
40°-50°	145.5	3.9
50°-60°	12.3	0.3
60°-70°	3.8	0.1
70°-80°	2.8	0.1
80°-90°	1.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2858.7	77.0
0°-40°	3547.2	95.5
0°-60°	3705.1	99.8
0°-90°	3713.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3713.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5230	
5°	5111	474
15°	4078	1133
25°	2744	1251
35°	1009	689
45°	164	146
55°	10	12
65°	4	4
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P364836

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8035-F6LBXVM1-LI-BL85

CANDELA DISTRIBUTION (FULL):

0°	
0°	5229.8
2.5°	5227.0
5°	5110.9
7.5°	4931.7
10°	4665.8
12.5°	4401.3
15°	4078.1
17.5°	3749.2
20°	3388.1
22.5°	3071.8
25°	2744.4
27.5°	2428.1
30°	2058.6
32.5°	1571.6
35°	1009.0
37.5°	680.1
40°	450.6
42.5°	281.3
45°	163.7
47.5°	84.0
50°	39.2
52.5°	16.8
55°	9.8
57.5°	7.0
60°	5.6
62.5°	4.2
65°	4.2
67.5°	2.8
70°	2.8
72.5°	4.2
75°	2.8
77.5°	1.4
80°	1.4
82.5°	1.4
85°	1.4
87.5°	1.4
90°	0.0

(END OF REPORT)