

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P365533

Luminaire Tested: **FLD6BX40D010-FEU6B35-8027-F6LBXVM1-MW-BTR89BI**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P365533  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-13)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD6BX40D010-FEU6B35-8027-F6LBXVM1-MW-BTR89BI  
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, MATTE WHITE REFLECTOR,  
BOTTOM TRIM ACRYLIC, CLEAR RFI 0.125", 4000LM  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2283.0 lumens  
Efficiency: N/A  
Efficacy: 56.2 lumens/watt  
Spacing Criteria (0/90/45): 0.87 / 0.87 / 0.84  
Luminous Opening: Circular (Dia: 0.44' x H: 0')  
CIE Type: Direct


Input Watts (W): 40.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P365533

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8027-F6LBXVM1-MW-BTR89BI

### Luminous Intensity Polar Plot





TEST NUMBER: P365533

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8027-F6LBXVM1-MW-BTR89BI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	103	109	106	104	101	102	100	98	99	97	95	95	94	92	90
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81
3	98	91	85	80	96	89	84	79	86	82	78	84	80	77	82	78	75	74
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67
5	87	77	70	65	85	76	70	65	74	68	64	72	67	64	71	66	63	61
6	82	72	65	60	80	71	64	59	69	63	59	68	62	58	66	62	58	56
7	77	67	60	55	76	66	59	55	65	59	54	63	58	54	62	57	54	52
8	73	62	56	51	72	62	55	51	61	55	50	59	54	50	58	54	50	48
9	69	59	52	47	68	58	52	47	57	51	47	56	51	47	55	50	47	45
10	66	55	49	44	65	55	48	44	54	48	44	53	48	44	52	47	44	42

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	157825
5°	154834
10°	147041
15°	137707
20°	125695
25°	104198
30°	75601
35°	52288
40°	38668
45°	31624
50°	27737
55°	24667
60°	21509
65°	18298
70°	14613
75°	10568
80°	7587
85°	8626



TEST NUMBER: P365533

CATALOG NUMBER: FLD6BX40D010-FEUG6B35-8027-F6LBXVM1-MW-BTR89BI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	201.3	8.8
10°-20°	519.4	22.8
20°-30°	594.1	26.0
30°-40°	385.2	16.9
40°-50°	245.6	10.8
50°-60°	176.9	7.7
60°-70°	107.5	4.7
70°-80°	42.8	1.9
80°-90°	10.0	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1314.9	57.6
0°-40°	1700.1	74.5
0°-60°	2122.6	93.0
0°-90°	2283.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2283.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2204	
5°	2154	201
15°	1858	519
25°	1319	594
35°	598	385
45°	312	246
55°	198	177
65°	108	108
75°	38	43
85°	10	10
90°	0	



TEST NUMBER: P365533

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8027-F6LBXVM1-MW-BTR89BI

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2204.2
2.5°	2191.1
5°	2154.2
7.5°	2093.6
10°	2022.4
12.5°	1943.4
15°	1857.7
17.5°	1766.8
20°	1649.6
22.5°	1499.4
25°	1318.9
27.5°	1121.2
30°	914.4
32.5°	736.5
35°	598.2
37.5°	492.8
40°	413.7
42.5°	355.7
45°	312.3
47.5°	278.0
50°	249.0
52.5°	222.7
55°	197.6
57.5°	172.6
60°	150.2
62.5°	129.1
65°	108.0
67.5°	88.3
70°	69.8
72.5°	54.0
75°	38.2
77.5°	26.4
80°	18.4
82.5°	11.9
85°	10.5
87.5°	5.3
90°	0.0

(END OF REPORT)